

SF-20KP0,25-2,50 - Crimp contact

1241953

<https://www.phoenixcontact.com/us/products/1241953>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



The figure may differ depending on the connection area

Crimp contact, Pin, turned, contact diameter: 2 mm, connection cross section: 0.25 mm² ... 2.5 mm², contact material: CuZn, Item is lead-free in accordance with RoHS II without Exemption 6c (Pb < 0.1 %)

Your advantages

- Crimping connection: vibration- and temperature-resistant assembly
- High tensile strength of the connection
- Low contact resistance
- Easy production monitoring

Commercial data

| | |
|--------------------------------------|---------------|
| Item number | 1241953 |
| Packing unit | 50 pc |
| Minimum order quantity | 50 pc |
| Sales key | AB38 |
| Product key | ABREBG |
| GTIN | 4063151455279 |
| Weight per piece (including packing) | 0.976 g |
| Weight per piece (excluding packing) | 0.88 g |
| Customs tariff number | 85366990 |
| Country of origin | DE |

SF-20KP0,25-2,50 - Crimp contact



1241953

<https://www.phoenixcontact.com/us/products/1241953>

Technical data

Product properties

| | |
|-----------------------|---------------|
| Product type | Crimp contact |
| Contact material type | turned |

Connection data

Connection technology

| | |
|-------------------------|------------------|
| Contact connection type | Pin |
| Connection method | Crimp connection |

Conductor connection

| | |
|--------------------------|--|
| Connection cross section | 0.25 mm ² ... 2.5 mm ² |
|--------------------------|--|

Material specifications

| | |
|--|------|
| Material Contact | CuZn |
| Material Metal surface contact area (middle layer) | Ni |
| Material Metal surface contact area (top layer) | Au |

Dimensions

| | |
|-----------------------------|------|
| Diameter (Contact diameter) | 2 mm |
|-----------------------------|------|

Mechanical properties

Mechanical data

| | |
|-----------------------------|-----|
| Insertion/withdrawal cycles | 100 |
|-----------------------------|-----|

SF-20KP0,25-2,50 - Crimp contact



1241953

<https://www.phoenixcontact.com/us/products/1241953>

Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-13.0 | 27440204 |
| ECLASS-15.0 | 27440204 |

ETIM

| | |
|-----------|----------|
| ETIM 10.0 | EC000796 |
|-----------|----------|

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 39121100 |
|-------------|----------|

SF-20KP0,25-2,50 - Crimp contact



1241953

<https://www.phoenixcontact.com/us/products/1241953>

Environmental product compliance

EU RoHS

| | |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

China RoHS

| | |
|--|--|
| Environment friendly use period (EFUP) | EFUP-E |
| | No hazardous substances above the limits |

EU REACH SVHC

| | |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com