HC-STA-B24/B16-CESFD-PL-BK - Housing

1252472

https://www.phoenixcontact.com/us/products/1252472

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Sleeve housing B24, for double locking latch, material: PA, straight, height: 99.5 mm, cable gland: none, Adapter sleeve for the CES cable entry system, Can be optimally combined with modular contact inserts

Product description

Adapter sleeve for combining the CES cable entry system with the pluggability of a HEAVYCON housing. By combining the CES cable entry system and the adapter sleeve, several conductors can be conveniently inserted into a connector.

Your advantages

- Labeling option using 9 x 20 mm marking label
- Simple assembly of multiple cables in a HEAVYCON housing
- Halogen-free plastic
- Marking label can be attached

Commercial data

Item number	1252472
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	BF67
Product key	AF7CZX
GTIN	4063151360610
Weight per piece (including packing)	221.33 g
Weight per piece (excluding packing)	211.05 g
Customs tariff number	85389099
Country of origin	CN

Technical data


Notes

General	For module carrier frame B24

Product properties

Product type	Housing with locking latch
Housing type	Sleeve housing
Type	B24
Cable outlet	straight
Pg screw connection	none

Dimensions

Dimensional drawing	
Width	57.3 mm
Height	99.5 mm
Length	122.2 mm

Material specifications

Housing material	PA

Mechanical properties

Mechanical data

Locking type	Pin

Mounting

Assembly note	The housing has to be extended by the B16 sealing frame with screw locking mechanism (Item No. 0801659). When combined with the sealing frame with screw locking mechanism, a simple assembly of multiple cables in a single HC housing is possible.


Environmental and real-life conditions

Ambient conditions

Degree of protection	IP54
Ambient temperature (operation)	-40 °C ... 125 °C

Drawings

Dimensional drawing



Dimensional drawing

Approvals

To download certificates, visit the product detail page: https://www.phoenixcontact.com/us/products/1252472

UL Recognized
Approval ID: E255026

cUL Recognized
Approval ID: E255026

Classifications

ECLASS

ECLASS-15.0	27440202
ECLASS-13.0	27440202

ETIM

ETIM 10.0	EC000437

UNSPSC

UNSPSC 21.0	31261500

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2026 © - all rights reserved
https://www.phoenixcontact.com

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com