

SAC-3P-M8MS/10,0-542/M8FS BK - Sensor/actuator cable



1257089

<https://www.phoenixcontact.com/us/products/1257089>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Sensor/actuator cable, 3-position, PVC, yellow, Plug straight M8, on Socket straight M8, cable length: 10 m

Commercial data

Item number	1257089
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	BF13
Product key	AF1IAA
GTIN	4063151363574
Weight per piece (including packing)	22.22 g
Weight per piece (excluding packing)	22.22 g
Country of origin	US

SAC-3P-M8MS/10,0-542/M8FS BK - Sensor/actuator cable



1257089

<https://www.phoenixcontact.com/us/products/1257089>

Technical data

Product properties

Product type	Sensor/actuator cable
Application	Standard, U.S. cables
Number of positions	3
No. of cable outlets	1
Shielded	no
Coding	A

Insulation characteristics

Overvoltage category	II
Degree of pollution	3

Material specifications

Flammability rating according to UL 94	HB
Seal material	NBR
Material of grip body	TPU, hardly inflammable, self-extinguishing
Contact material	CuSn
Contact surface material	Ni/Au
Contact carrier material	TPU GF
Material for screw connection	Zinc die-cast, nickel-plated
Outer sheath, material	PVC

Electrical properties

Insulation resistance	$\geq 100 \text{ M}\Omega$
Nominal voltage U_N	48 V AC
	60 V DC
Nominal current I_N	4 A

Mechanical properties

Mechanical data

Insertion/withdrawal cycles	≥ 100
-----------------------------	------------

Signaling

Status display	no
Status display present	no

Connection data

Conductor connection

Tightening torque	0.2 Nm (M8 connectors)
-------------------	------------------------

Connector

SAC-3P-M8MS/10,0-542/M8FS BK - Sensor/actuator cable



1257089

<https://www.phoenixcontact.com/us/products/1257089>

Connection 1

Type	Plug straight M8
Number of positions	3

Connection 2

Type	Socket straight M8
Number of positions	3

Cable/line

Cable length	10 m
--------------	------

PVC yellow 105 °C [542]

Dimensional drawing	
Cable weight	21 kg/km
UL AWM Style	2517 (105 °C / 300 V)
Number of positions	3
Shielded	no
Cable type	PVC yellow 105 °C [542]
Conductor structure signal line	7x 0.20 mm
AWG signal line	24
Wire diameter incl. insulation	1.12 mm ±0.03 mm
External cable diameter	4.10 mm ±0.2 mm
Outer sheath, material	PVC
External sheath, color	yellow
Conductor material	Tin-plated Cu litz wires
Material wire insulation	PVC
Single wire, color	brown, blue, black
Overall twist	3 wires, twisted
Max. conductor resistance	max. 79.7 Ω/km (20 °C)
Insulation resistance	≥ (550 M Ohms/m @ 500V)
Nominal voltage, cable	300 V
Minimum bending radius, flexible installation	8 x D
Smallest bending radius, movable installation	33 mm
Flame resistance	FT4
Other resistance	UV resistant
Ambient temperature (operation)	-30 °C ... 105 °C (cable, fixed installation)

SAC-3P-M8MS/10,0-542/M8FS BK - Sensor/actuator cable



1257089

<https://www.phoenixcontact.com/us/products/1257089>

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP65
	IP67
	IP68

Standards and regulations

Standard designation	M8 connector
Standards/specifications	IEC 61076-2-104

SAC-3P-M8MS/10,0-542/M8FS BK - Sensor/actuator cable

1257089

<https://www.phoenixcontact.com/us/products/1257089>

Drawings

Dimensional drawing



M8 x 1 male plug, straight version

Dimensional drawing



Socket M8 x 1, straight

SAC-3P-M8MS/10,0-542/M8FS BK - Sensor/actuator cable

1257089

<https://www.phoenixcontact.com/us/products/1257089>

Schematic diagram



Pin assignment M8 plug, 3-pos., view male side

Schematic diagram



Pin assignment M8 socket, 3-pos., view female side


SAC-3P-M8MS/10,0-542/M8FS BK - Sensor/actuator cable



1257089

<https://www.phoenixcontact.com/us/products/1257089>

Circuit diagram



Contact assignment of M8 plugs/sockets

SAC-3P-M8MS/10,0-542/M8FS BK - Sensor/actuator cable



1257089

<https://www.phoenixcontact.com/us/products/1257089>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1257089>

 UL Listed Approval ID: FILE E 221474				
	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
keine				
	60 V	4 A	-	-

 cUL Listed Approval ID: FILE E 221474				
	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
keine				
	60 V	4 A	-	-

SAC-3P-M8MS/10,0-542/M8FS BK - Sensor/actuator cable



1257089

<https://www.phoenixcontact.com/us/products/1257089>

Classifications

ECLASS

ECLASS-13.0	27060311
ECLASS-15.0	27060311

ETIM

ETIM 10.0	EC001855
-----------	----------

SAC-3P-M8MS/10,0-542/M8FS BK - Sensor/actuator cable



1257089

<https://www.phoenixcontact.com/us/products/1257089>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com