

UM 108-PROFIL 15,40CM BK - Profile



1270126

<https://www.phoenixcontact.com/us/products/1270126>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Press-drawn section housings, Latching with side elements, latching with foot element, Basic profile, profile width (internal): 122.6 mm, profile width (external): 107.5 mm, length: 154 mm, depth: 21.5 mm



The figure shows the variant UM 45-Profil CM

Commercial data

Item number	1270126
Packing unit	10 pc
Minimum order quantity	10 pc
Note	Made to order (non-returnable)
Product key	ACHDBB
GTIN	4063151428013
Weight per piece (including packing)	95.45 g
Weight per piece (excluding packing)	95.45 g
Country of origin	DE

UM 108-PROFIL 15,40CM BK - Profile



1270126

<https://www.phoenixcontact.com/us/products/1270126>

Technical data

Product properties

Product type	Component housing lower part
Housing type	Press-drawn section housings
Housing type	Extruded profile housings
Housing series	UM
Product family	UM108
Ventilation openings present	no

Dimensions

Depth	21.5 mm
Length	154 mm

External dimensions

Profile width (external)	107.5 mm
--------------------------	----------

Internal dimensions

Profile width (internal)	122.6 mm
--------------------------	----------

Material specifications

Color (Profile)	black (RAL 9005)
Material Profile	PVC

PCB data

Number of PCB holders	2
-----------------------	---

Mounting

Mounting type	Latching with side elements, latching with foot element
---------------	---

UM 108-PROFIL 15,40CM BK - Profile



1270126

<https://www.phoenixcontact.com/us/products/1270126>

Classifications

ECLASS

ECLASS-13.0	27190601
ECLASS-15.0	27190601

ETIM

ETIM 10.0	EC002779
-----------	----------

UNSPSC

UNSPSC 21.0	31261500
-------------	----------

UM 108-PROFIL 15,40CM BK - Profile



1270126

<https://www.phoenixcontact.com/us/products/1270126>

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
China RoHS	
Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com