

SAC-4P-P12MS/0,15-PUR - Sensor/actuator cable



1324457

<https://www.phoenixcontact.com/us/products/1324457>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Sensor/actuator cable, Universal, 4-position, PUR halogen-free, black-gray RAL 7021, Plug straight Push Pull, coding: A, on free cable end, cable length: 0.15 m

Commercial data

Item number	1324457
Packing unit	1 pc
Minimum order quantity	1 pc
Product key	AF1CCC
GTIN	4063151614522
Weight per piece (including packing)	15.8 g
Weight per piece (excluding packing)	15.7 g
Country of origin	PL

SAC-4P-P12MS/0,15-PUR - Sensor/actuator cable



1324457

<https://www.phoenixcontact.com/us/products/1324457>

Technical data

Product properties

Product type	Sensor/actuator cable
Number of positions	4
Shielded	no

Insulation characteristics

Overvoltage category	II
Degree of pollution	3

Electrical properties

Nominal voltage U_N	250 V AC
	250 V DC
Nominal current I_N	4 A

Connection data

Conductor connection

Tightening torque	0.4 Nm
-------------------	--------

Connector

Connection 1

Locking type	Push Pull
--------------	-----------


Connection 2

Type	free cable end
------	----------------

Cable/line

Cable length	0.15 m
--------------	--------

PUR halogen-free black [PUR]

Dimensional drawing	
Cable weight	30 kg/km
UL AWM Style	20549 / 10493 (80°C/300 V)
Number of positions	4
Shielded	no
Cable type	PUR halogen-free black [PUR]

SAC-4P-P12MS/0,15-PUR - Sensor/actuator cable



1324457

<https://www.phoenixcontact.com/us/products/1324457>

Conductor structure signal line	42x 0.10 mm
AWG signal line	22
Conductor cross-section	4x 0.34 mm ² (Signal line)
Wire diameter incl. insulation	1.27 mm ±0.02 mm
External cable diameter	4.20 mm ±0.15 mm
Outer sheath, material	PUR
External sheath, color	black-gray RAL 7021
Conductor material	Bare Cu litz wires
Material wire insulation	PP
Single wire, color	brown, white, blue, black
Thickness, insulation	≥ 0.21 mm
Thickness, outer sheath	approx. 0.50 mm
Overall twist	4 wires, twisted
Max. conductor resistance	≤ 58 Ω/km
Insulation resistance	≥ 1 GΩ*km
Nominal voltage, cable	≤ 300 V
Test voltage	≥ 3000 V
Minimum bending radius, fixed installation	5 x D
Minimum bending radius, flexible installation	10 x D
Smallest bending radius, fixed installation	21 mm
Smallest bending radius, movable installation	42 mm
Dynamic load capacity (bending)	Max. bending cycles: 10000000, Bending radius: 42 mm, Bending radius: 10 x D, Traversing path: 10 m, Traversing rate: 3 m/s, Acceleration: 10 m/s ²
Dynamic load capacity (torsion)	Torsion: ±180 °/m, Torsion cycles: ≥5000000, Torsional frequency: 35 cycles/min.
Halogen-free	in accordance with DIN VDE 0472 part 815 in accordance with DIN EN 50267-2-1
Flame resistance	in accordance with UL 758/1581 FT2 DIN EN 60332-2-2 (20 s)
Resistance to oil	in accordance with DIN EN 60811-2-1
Other resistance	Highly resistant to acids, alkaline solutions and solvents hydrolysis and microbe resistant partly UV-resistant (in accordance with DIN EN ISO 4892-2-A) Low adhesion abrasion-resistant
Special properties	Flexible cable conduit capable Silicone-free Free of substances which would hinder coating with paint or varnish flexible
Ambient temperature (operation)	-40 °C ... 80 °C (cable, fixed installation) -25 °C ... 80 °C (Cable, flexible installation)

Environmental and real-life conditions

SAC-4P-P12MS/0,15-PUR - Sensor/actuator cable



1324457

<https://www.phoenixcontact.com/us/products/1324457>

Ambient conditions

Degree of protection	IP65
	IP67
	IP68

SAC-4P-P12MS/0,15-PUR - Sensor/actuator cable




1324457

<https://www.phoenixcontact.com/us/products/1324457>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1324457>

 cULus Listed Approval ID: E221474				
	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
keine				
	300 V	4 A	- 22	-

SAC-4P-P12MS/0,15-PUR - Sensor/actuator cable



1324457

<https://www.phoenixcontact.com/us/products/1324457>

Classifications

ECLASS

ECLASS-13.0	27060311
ECLASS-15.0	27060311

ETIM

ETIM 10.0	EC001855
-----------	----------

UNSPSC

UNSPSC 21.0	26121600
-------------	----------

SAC-4P-P12MS/0,15-PUR - Sensor/actuator cable



1324457

<https://www.phoenixcontact.com/us/products/1324457>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com