

# HSC-LR 3U KIT 7035 - Locking



1326357

<https://www.phoenixcontact.com/us/products/1326357>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



DIN rail housing, 3U, Lock and Release system, width: 16.1 mm, height: 45.95 mm, depth: 8.8 mm, color: light gray (similar RAL 7035)

## Your advantages

- Easy, tool-free mounting
- Lock and Release interlock in contrasting color for intuitive operation
- Plastic in accordance with UL94 V0: for more rigorous flammability requirements

## Commercial data

|                                      |                                |
|--------------------------------------|--------------------------------|
| Item number                          | 1326357                        |
| Packing unit                         | 10 pc                          |
| Minimum order quantity               | 100 pc                         |
| Note                                 | Made to order (non-returnable) |
| Product key                          | ACHECZ                         |
| GTIN                                 | 4063151615871                  |
| Weight per piece (including packing) | 3.75 g                         |
| Weight per piece (excluding packing) | 3.73 g                         |
| Country of origin                    | DE                             |

## Technical data

### Notes

|               |                                                           |
|---------------|-----------------------------------------------------------|
| Assembly note | Please observe the application note in the download area. |
|---------------|-----------------------------------------------------------|

### Product properties

|                |                   |
|----------------|-------------------|
| Product type   | Mounting material |
| Housing type   | DIN rail housing  |
| Housing series | ME-IO             |
| Product family | ME-IO             |

### Dimensions

|        |          |
|--------|----------|
| Width  | 16.1 mm  |
| Height | 45.95 mm |
| Depth  | 8.8 mm   |

### Material specifications

|                                        |                       |
|----------------------------------------|-----------------------|
| Color                                  | light gray (RAL 7035) |
| Material                               | PA6-GF30              |
| Flammability rating according to UL 94 | V0                    |

### Environmental and real-life conditions

#### Ambient conditions

|                                         |                                                    |
|-----------------------------------------|----------------------------------------------------|
| Max. IP code to attain                  | IP20                                               |
| Ambient temperature (operation)         | -40 °C ... 105 °C (depending on power dissipation) |
| Ambient temperature (storage/transport) | -40 °C ... 55 °C                                   |
| Ambient temperature (assembly)          | -5 °C ... 100 °C                                   |
| Relative humidity (storage/transport)   | 80 %                                               |

### Mounting

|               |         |
|---------------|---------|
| Mounting type | Snap in |
|---------------|---------|

### Packaging specifications

|                      |                     |
|----------------------|---------------------|
| Type of packaging    | packed in cardboard |
| Outer packaging type | Carton              |

# HSC-LR 3U KIT 7035 - Locking



1326357

<https://www.phoenixcontact.com/us/products/1326357>

## Approvals

🔗 To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1326357>



**UL Recognized**

Approval ID: E240868

# HSC-LR 3U KIT 7035 - Locking



1326357

<https://www.phoenixcontact.com/us/products/1326357>

## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-13.0 | 27190605 |
| ECLASS-15.0 | 27190605 |

### ETIM

|           |          |
|-----------|----------|
| ETIM 10.0 | EC002779 |
|-----------|----------|

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 31261500 |
|-------------|----------|

# HSC-LR 3U KIT 7035 - Locking



1326357  
<https://www.phoenixcontact.com/us/products/1326357>

## Environmental product compliance

|                                         |                                          |
|-----------------------------------------|------------------------------------------|
| EU RoHS                                 |                                          |
| Fulfills EU RoHS substance requirements | Yes, No exemptions                       |
| China RoHS                              |                                          |
| Environment friendly use period (EFUP)  | EFUP-E                                   |
|                                         | No hazardous substances above the limits |
| EU REACH SVHC                           |                                          |
| REACH candidate substance (CAS No.)     | No substance above 0.1 wt%               |
| EF3.1 Climate Change                    |                                          |
| CO2e kg                                 | 0.039 kg CO2e                            |

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)