

NBC-HDMI-HAM/5,0-PVC/HAM - HDMI cable



1332084

<https://www.phoenixcontact.com/us/products/1332084>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



HDMI cable, degree of protection: IP20, cable length: 5 m, number of positions: 19, material: LCP, HDMI High Speed

Your advantages

- HDMI high-speed patch cables
- Integrated network transmission thanks to HDMI Ethernet channel
- Reliable transmission of 4K videos

Commercial data

| | |
|--------------------------------------|---------------|
| Item number | 1332084 |
| Packing unit | 1 pc |
| Minimum order quantity | 1 pc |
| Sales key | AB14 |
| Product key | ABNEBA |
| GTIN | 4063151627898 |
| Weight per piece (including packing) | 326 g |
| Weight per piece (excluding packing) | 326 g |
| Customs tariff number | 85444290 |
| Country of origin | CN |

NBC-HDMI-HAM/5,0-PVC/HAM - HDMI cable



1332084

<https://www.phoenixcontact.com/us/products/1332084>

Technical data

Product properties

| | |
|---------------------|-------------------------|
| Product type | Data cable preassembled |
| Sensor type | HDMI High Speed |
| Number of positions | 19 |
| Shielded | yes |

Electrical properties

| | |
|--------------------------|----------------|
| Insulation resistance | 100 M Ω |
| Test voltage | 500 V AC |
| Test voltage Core/Core | 500 V AC |
| Test voltage Core/Shield | 500.00 V AC |
| Wave impedance | 100 Ω |

Mechanical properties

Mechanical data

| | |
|-----------------------------|---------|
| Insertion/withdrawal cycles | > 10000 |
|-----------------------------|---------|

Material specifications

| | |
|--|---------|
| Color of the housing part | black |
| Flammability rating according to UL 94 | UL94 V0 |
| Housing material | LCP |

Dimensions

| | |
|--------|---------|
| Width | 20.3 mm |
| Height | 12 mm |
| Length | 49.3 mm |

Connector

Connection 1

| | |
|-----------------------------|---------------------------|
| Type | Plug straight HDMI type A |
| Shielded | yes |
| Insertion/withdrawal cycles | > 10000 |
| Insulation resistance | 100 M Ω |
| Degree of protection | IP20 |

Connection 2

| | |
|----------------------|---------------------------|
| Type | Plug straight HDMI type A |
| Degree of protection | IP20 |

Cable/line

| | |
|--------------|--------|
| Cable length | 5.00 m |
|--------------|--------|

NBC-HDMI-HAM/5,0-PVC/HAM - HDMI cable



1332084

<https://www.phoenixcontact.com/us/products/1332084>

PVC HDMI high speed black [HDMI]

| | |
|---------------------------|---------------------------|
| Shielded | yes |
| UL AWM Style | 20276 |
| Cable type | PVC HDMI high speed black |
| Cable type (abbreviation) | HDMI |
| External cable diameter | 6.00 mm |
| Outer sheath, material | PVC |
| External sheath, color | black |
| Shielding | Aluminum-lined foil |

NBC-HDMI-HAM/5,0-PVC/HAM - HDMI cable



1332084

<https://www.phoenixcontact.com/us/products/1332084>

Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-13.0 | 27060307 |
| ECLASS-15.0 | 27060307 |

ETIM

| | |
|-----------|----------|
| ETIM 10.0 | EC001855 |
|-----------|----------|

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 39121400 |
|-------------|----------|

NBC-HDMI-HAM/5,0-PVC/HAM - HDMI cable



1332084

<https://www.phoenixcontact.com/us/products/1332084>

Environmental product compliance

EU RoHS

| | |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

China RoHS

| | |
|--|--|
| Environment friendly use period (EFUP) | EFUP-E |
| | No hazardous substances above the limits |

EU REACH SVHC

| | |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com