

D3HC-MP 0.20-0.50-M-SN-L - Crimp contact



1340368

<https://www.phoenixcontact.com/us/products/1340368>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Crimp contact, nominal current: 6 A, contact surface: Tin, product range: D3HC-MP-M



Commercial data

| | |
|--------------------------------------|--------------------------------|
| Item number | 1340368 |
| Packing unit | 200 pc |
| Minimum order quantity | 200 pc |
| Note | Made to order (non-returnable) |
| Sales key | AA02 |
| Product key | AABCUA |
| GTIN | 4063151644673 |
| Weight per piece (including packing) | 0.452 g |
| Weight per piece (excluding packing) | 0.448 g |
| Customs tariff number | 85366990 |
| Country of origin | CN |

D3HC-MP 0.20-0.50-M-SN-L - Crimp contact



1340368

<https://www.phoenixcontact.com/us/products/1340368>

Technical data

Product properties

| | |
|----------------|---------------|
| Product type | Crimp contact |
| Product family | D3HC-MP-M |

Connection data

| | |
|-----------------------------|-----------|
| Stripping length | 4.5 mm |
| Conductor cross-section AWG | 24 ... 20 |

Material specifications

| | |
|--|--------------------|
| Contact surface | Tin Sn |
| Contact surface material | Tin |
| Metal surface terminal point (top layer) | Tin (1 - 3 µm Sn) |
| Metal surface contact area (top layer) | Tin (1 - 3 µm Sn) |
| Surface characteristics | hot-dip tin-plated |
| Contact material | Cu alloy |

Electrical properties

| | |
|-----------------------|-----|
| Nominal current I_N | 6 A |
|-----------------------|-----|

D3HC-MP 0.20-0.50-M-SN-L - Crimp contact



1340368

<https://www.phoenixcontact.com/us/products/1340368>

Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-13.0 | 27460291 |
| ECLASS-15.0 | 27460291 |

ETIM

| | |
|-----------|----------|
| ETIM 10.0 | EC002943 |
|-----------|----------|

D3HC-MP 0.20-0.50-M-SN-L - Crimp contact



1340368

<https://www.phoenixcontact.com/us/products/1340368>

Environmental product compliance

EU RoHS

| | |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

EU REACH SVHC

| | |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com