

HC-STA-B48-HHFS-5TTM25-EM-AL - Housing



1345274

<https://www.phoenixcontact.com/us/products/1345274>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Sleeve housing B48, for single locking latch, material: Die-cast aluminum, salt water resistant, cable outlets: 5, straight, M25, height: 107.5 mm, cable gland: none, Standard

Your advantages

- Good shielding in the event of electromagnetic interference

Commercial data

Item number	1345274
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	BF56
Product key	AF7APB
GTIN	4063151658649
Weight per piece (including packing)	580.8 g
Weight per piece (excluding packing)	580 g
Customs tariff number	85389099
Country of origin	CN

HC-STA-B48-HHFS-5TTM25-EM-AL - Housing



1345274


<https://www.phoenixcontact.com/us/products/1345274>

Technical data

Product properties

Product type	Housing with locking latch
Housing type	Sleeve housing
Application	Standard
Type	B48
No. of cable outlets	5
Type of the screw connection	M25
Cable outlet	straight
Pg screw connection	none

Dimensions

Dimensional drawing	
Width	90 mm
Height	107.5 mm
Length	132 mm

Material specifications

Housing material	Die-cast aluminum, salt water resistant
Housing surface material	uncoated

Mechanical properties

Mechanical data

Type of the screw connection	M25
Locking type	Pin

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP66
	IP67
Enclosure rating (NEMA)	4 (UL 50e)
	4X (UL 50e)
	12 (UL 50e)
Impact strength	IK08
Ambient temperature (operation)	-40 °C ... 125 °C

HC-STA-B48-HHFS-5TTM25-EM-AL - Housing




1345274

<https://www.phoenixcontact.com/us/products/1345274>

Drawings

Dimensional drawing



Dimensional drawing

HC-STA-B48-HHFS-5TTM25-EM-AL - Housing



1345274

<https://www.phoenixcontact.com/us/products/1345274>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1345274>



cUL Recognized
Approval ID: E255026



UL Recognized
Approval ID: E255026

1345274

<https://www.phoenixcontact.com/us/products/1345274>

Classifications

ECLASS

ECLASS-15.0	27440202
ECLASS-13.0	27440202

ETIM

ETIM 10.0	EC000437
-----------	----------

UNSPSC

UNSPSC 21.0	31261500
-------------	----------

1345274

<https://www.phoenixcontact.com/us/products/1345274>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com