

# CRIMPFOX DUO 16S SET - Tool set



1367687

<https://www.phoenixcontact.com/us/products/1367687>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Cutting, stripping, and crimping set, packaged in a tool case, comprising WIREFOX 10, WIREFOX 16/SB, CRIMPFOX DUO 16S, AI SORTI BOX RD, AI SORTI BOX ANT, TOOL-KIT STANDARD EMPTY

## Product description

Tool set, equipped

## Your advantages

- We have put together a number of attractive tool sets for you by selecting products from our comprehensive range of professional tools

## Commercial data

Item number	1367687
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	BH31
Product key	BH3521
GTIN	4063151722128
Weight per piece (including packing)	1,102 g
Weight per piece (excluding packing)	1,100 g
Customs tariff number	82060000
Country of origin	DE

# CRIMPFOX DUO 16S SET - Tool set



1367687

<https://www.phoenixcontact.com/us/products/1367687>

## Set consists of

### CRIMPFOX DUO 16S - Crimping pliers

1202877

<https://www.phoenixcontact.com/us/products/1202877>



Crimping pliers, contact type: insulated and uninsulated ferrules, standards/regulations: DIN 46228-1, DIN 46228-4, UL 486F, Form A, E, F, cross-section, minimum: 0.14 mm<sup>2</sup>, cross-section, maximum: 16 mm<sup>2</sup>, for TWIN ferrules up to 2 mm<sup>2</sup> x 6 mm<sup>2</sup>, automatic cross-section adjustment, rotating dies, lateral and front entry, crimping: square

---

### WIREFOX 10 - Stripping tool

1212150

<https://www.phoenixcontact.com/us/products/1212150>



Stripping tool, for cables and conductors from 0.02 - 10 mm<sup>2</sup>, self-adjusting, stripping length of up to 18 mm, cutting capacity of up to 10 mm<sup>2</sup> stranded/1.5 mm<sup>2</sup> solid, replaceable stripping blade

# CRIMPFOX DUO 16S SET - Tool set



1367687

<https://www.phoenixcontact.com/us/products/1367687>

## WIREFOX 16/SB - Spare knife

1212153

<https://www.phoenixcontact.com/us/products/1212153>



Replacement blade for WIREFOX 16, for cables and conductors of 4 - 16 mm<sup>2</sup>

---

## AI SORTI BOX RD - Assortment box

3202960

<https://www.phoenixcontact.com/us/products/3202960>



Assortment box, supplied with ferrules according to DIN 46228-4: 1990-09, 50 pcs. of each. AI 0,5-8 WH, AI 2,5-8 BU, 100 pcs. AI 0,75-8 GY, AI 1-8 RD, AI 1,5-8 BK

# CRIMPFOX DUO 16S SET - Tool set



1367687

<https://www.phoenixcontact.com/us/products/1367687>

## AI SORTI BOX ANT - Assortment box

3202973

<https://www.phoenixcontact.com/us/products/3202973>



**Assortment box**, supplied with ferrules in accordance with DIN 46228-4, 50 pcs. AI 4-10 GY, 20 pcs. each AI 6-12 YE, AI 10-12 RD, 10 pcs. AI 16-12 BU

---

## TOOL-KIT STANDARD EMPTY - Toolbag, unequipped

1212423

<https://www.phoenixcontact.com/us/products/1212423>



**Tool box**, unequipped

# CRIMPFOX DUO 16S SET - Tool set



1367687

<https://www.phoenixcontact.com/us/products/1367687>

## Technical data

### Product properties

Product type	Tool set
Type of packaging	Bag
Compression	Square crimp

### Crimping position 1

Min. cross section	16 mm <sup>2</sup>
Max. cross section	0.14 mm <sup>2</sup>
AWG min	26
AWG max	6

### Electrical properties

Fuse	DIN 46228-1, DIN 46228-4, UL 486F, form A, E, F
------	---

### Dimensions

Width	65 mm
Height	315 mm
Length	165 mm

### Material specifications

Color	black (RAL 9005)
-------	------------------

# CRIMPFOX DUO 16S SET - Tool set



1367687

<https://www.phoenixcontact.com/us/products/1367687>

## Classifications

### ECLASS

ECLASS-13.0	21045003
ECLASS-15.0	21045003

### ETIM

ETIM 10.0	EC000149
-----------	----------

### UNSPSC

UNSPSC 21.0	27113200
-------------	----------

# CRIMPFOX DUO 16S SET - Tool set



1367687

<https://www.phoenixcontact.com/us/products/1367687>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Not applicable, No electrical and electronic equipment (EEE), cannot be used in EEE
---	---

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)