VS-ASI-FC-SEAL-HP - Seal

1400374

https://www.phoenixcontact.com/us/products/1400374

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



End sealing for AS-Interface flat-ribbon conductor, can be used on both sides, IP67 degree of protection:

Commercial data


Item number	1400374
Packing unit	10 pc
Minimum order quantity	1 pc
Sales key	BF46
Product key	AF3ZAX
GTIN	4046356495080
Weight per piece (including packing)	8.23 g
Weight per piece (excluding packing)	8.23 g
Customs tariff number	85389099
Country of origin	PL

Technical data

Product properties

Product type	Seal

Dimensions

Dimensional drawing	
Width	22 mm
Depth	22 mm
Length	36 mm
Wrench size, union nut	19 mm
Wrench size, support	19 mm

Material specifications

Material	PA
Seal material	NBR


Environmental and real-life conditions

Ambient conditions

Degree of protection	IP67
Ambient temperature (operation)	-20 °C ... 70 °C

Drawings

Dimensional drawing



Classifications

ECLASS

ECLASS-13.0	27440192
ECLASS-15.0	27440192

ETIM

ETIM 10.0	EC002943

UNSPSC

UNSPSC 21.0	39121400

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%

EF3.1 Climate Change

CO2e kg	0.822 kg CO2e

Phoenix Contact 2026 © - all rights reserved
https://www.phoenixcontact.com

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com