

# Q2-FLA16-0,75 VERB BK - Conductor connector



1403390

<https://www.phoenixcontact.com/us/products/1403390>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



QUICKON cable connector, 4-pos., connection cross section 0.34-0.75 mm<sup>2</sup>, only flange with contacts of Order No. 1642140

## Commercial data

Item number	1403390
Packing unit	50 pc
Minimum order quantity	50 pc
Product key	AF6CBA
GTIN	4046356650748
Weight per piece (including packing)	7.076 g
Weight per piece (excluding packing)	7.113 g
Country of origin	DE

# Q2-FLA16-0,75 VERB BK - Conductor connector



1403390

<https://www.phoenixcontact.com/us/products/1403390>

## Classifications

### ECLASS

ECLASS-13.0	27440113
ECLASS-15.0	27440113

### ETIM

ETIM 10.0	EC002636
-----------	----------

### UNSPSC

UNSPSC 21.0	39121400
-------------	----------

# Q2-FLA16-0,75 VERB BK - Conductor connector



1403390

<https://www.phoenixcontact.com/us/products/1403390>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)