

VS-MP-PPC/CG-PO/10G - Coupling



1403682

<https://www.phoenixcontact.com/us/products/1403682>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Coupling, design: Version 14, degree of protection: IP65, CAT6_A, material: Metal, connection method: Spring-cage connection, color: black

Product description

Push/pull power and data coupling; version 14

Commercial data

Item number	1403682
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	AB17
Product key	ABNOGA
GTIN	4046356664318
Weight per piece (including packing)	464.7 g
Weight per piece (excluding packing)	392.853 g
Customs tariff number	85366990
Country of origin	DE

VS-MP-PPC/CG-PO/10G - Coupling



1403682

<https://www.phoenixcontact.com/us/products/1403682>

Technical data

Product properties

Product type	Network distributor box
Type	Version 14
Connection profile	Power
Number of slots	2

Electrical properties

Rated voltage (III/3)	72 V (DC)
Transmission medium	Copper
Transmission characteristics (category)	CAT6 _A

Connection data

Connection technology

Connection method	Spring-cage connection
-------------------	------------------------

Dimensions

Width	66 mm
Height	51 mm
Length	115 mm

Material specifications

Color	black
Housing material	Metal

Cable/line

External cable diameter	5 mm ... 8 mm (Data cable gland)
-------------------------	----------------------------------

Mechanical properties

Mechanical data

Insertion/withdrawal cycles	> 1000 (Data)
-----------------------------	---------------

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP65
Ambient temperature (operation)	-40 °C ... 70 °C

Mounting

Mounting type	Screw mounting
---------------	----------------

VS-MP-PPC/CG-PO/10G - Coupling


1403682

<https://www.phoenixcontact.com/us/products/1403682>



Drawings

Drilling plan/solder pad geometry



VS-MP-PPC/CG-PO/10G - Coupling



1403682

<https://www.phoenixcontact.com/us/products/1403682>

Classifications

ECLASS

ECLASS-13.0	27061801
ECLASS-15.0	27440325

UNSPSC

UNSPSC 21.0	43222600
-------------	----------

VS-MP-PPC/CG-PO/10G - Coupling



1403682

<https://www.phoenixcontact.com/us/products/1403682>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c)

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
	6,6'-di-tert-butyl-2,2'-methylenedi-p-cresol(CAS: 119-47-1)
SCIP	ff8f431e-a2fd-45cb-b832-836fa1eed320

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com