

# VS-MP-PPC/PPC-1G - Coupling



1403685

<https://www.phoenixcontact.com/us/products/1403685>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Coupling, design: Version 14, degree of protection: IP65, number of positions: 8, 1 Gbps, CAT5, material: Metal, connection method: Coupling, color: black, Ethernet

## Product description

Push/pull data coupling; version 14

## Your advantages

- Permanent mounting is also an option
- Including covers for protection against environmental influences
- Robust design

## Commercial data

Item number	1403685
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	AB17
Product key	ABNOFB
GTIN	4046356664349
Weight per piece (including packing)	257.1 g
Weight per piece (excluding packing)	183.626 g
Customs tariff number	85366990
Country of origin	PL

# VS-MP-PPC/PPC-1G - Coupling



1403685

<https://www.phoenixcontact.com/us/products/1403685>

## Technical data

### Product properties

Product type	Network distributor box
Type	Version 14
Sensor type	Ethernet
Number of positions	8
Connection profile	RJ45
Number of slots	1

### Electrical properties

Maximum load current	1.5 A
Rated voltage (III/3)	72 V (DC)
Rated surge voltage	30 V
Transmission medium	Copper
Transmission speed	1 Gbps
Transmission characteristics (category)	CAT5

### Connection data

#### Connection technology

Connection method	Coupling
-------------------	----------

### Dimensions

Width	38 mm
Height	51 mm
Length	115 mm

### Material specifications

Color	black
Flammability rating according to UL 94	V0
Housing material	Metal
Contact material	Phosphor bronze

### Mechanical properties

#### Mechanical data

Insertion/withdrawal cycles	≥ 750 (Data)
-----------------------------	--------------

### Environmental and real-life conditions

#### Ambient conditions

Degree of protection	IP65
Ambient temperature (operation)	-40 °C ... 70 °C
Ambient temperature (storage/transport)	-40 °C ... 70 °C

# VS-MP-PPC/PPC-1G - Coupling



1403685

<https://www.phoenixcontact.com/us/products/1403685>

## Mounting

Mounting type	Screw mounting
---------------	----------------


# VS-MP-PPC/PPC-1G - Coupling

1403685

<https://www.phoenixcontact.com/us/products/1403685>



## Drawings



# VS-MP-PPC/PPC-1G - Coupling



1403685

<https://www.phoenixcontact.com/us/products/1403685>

## Classifications

### ECLASS

ECLASS-13.0	27061801
ECLASS-15.0	27440325

### UNSPSC

UNSPSC 21.0	39121400
-------------	----------

# VS-MP-PPC/PPC-1G - Coupling



1403685

<https://www.phoenixcontact.com/us/products/1403685>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

### EU REACH SVHC

REACH candidate substance (CAS No.)	6,6'-di-tert-butyl-2,2'-methylenedi-p-cresol(CAS: 119-47-1)
SCIP	48ea2a4a-82ed-4d99-ac27-b76ce4a05f12

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)