

# SAC-12P-M23FS/3-35T/FS AMK 161 - Sensor/actuator cable



1405409

<https://www.phoenixcontact.com/us/products/1405409>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Sensor/actuator cable, 12-pos., PUR/PVC, RAL 9005 (black), shielded, straight M12 SPEEDCON socket (A-coded) to straight M23 socket, cable length: 3 m

## Commercial data

|                                      |               |
|--------------------------------------|---------------|
| Item number                          | 1405409       |
| Packing unit                         | 1 pc          |
| Minimum order quantity               | 50 pc         |
| Product key                          | AF1CNA        |
| GTIN                                 | 4046356744157 |
| Weight per piece (including packing) | 393 g         |
| Weight per piece (excluding packing) | 22.22 g       |
| Country of origin                    | DE            |

# SAC-12P-M23FS/3-35T/FS AMK 161 - Sensor/actuator cable



1405409

<https://www.phoenixcontact.com/us/products/1405409>

## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-13.0 | 27060311 |
| ECLASS-15.0 | 27060311 |

# SAC-12P-M23FS/3-35T/FS AMK 161 - Sensor/actuator cable



1405409

<https://www.phoenixcontact.com/us/products/1405409>

## Environmental product compliance

### China RoHS

|                                        |                                                                                                                                                                                                                                   |
|----------------------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Environment friendly use period (EFUP) | EFUP-50                                                                                                                                                                                                                           |
|                                        | An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required. |

### EU REACH SVHC

|                                     |                            |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)