

FOC-SC:A-SC:A-GZ03/... - FO patch cable



1405699

<https://www.phoenixcontact.com/us/products/1405699>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Assembled FO cable, zip cord cable, multi-mode fiberglass 50/125 μm , OM4, plug: SC/SC, degree of protection: IP20, for installation in cable ducts or control cabinets



Your advantages

- Multimode patch cable with outstanding optical and mechanical properties for indoor installation
- Ideal for use in distributor systems and for connecting termination devices
- Fire protection with LSZH sheath and UL 94 V0 components
- Interferometer tests at every stage of the certification process
- Satisfies optical and mechanical industry standards
- Connector with UPC polishing for optimum attenuation values

Commercial data

Item number	1405699
Packing unit	1 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Sales key	AB50
Product key	ABNIBC
Customs tariff number	85447000
Country of origin	DE

1405699

<https://www.phoenixcontact.com/us/products/1405699>

Technical data

Product properties

Product type	Data cable preassembled
Number of positions	2
No. of conductors	2
Number of slots	2

Electrical properties

Transmission medium	Multi-mode fiberglass
Transmission speed	10 Gbps
Transmission speed	10 Gbps

Mechanical properties

Tensile strength short-term/long-term	50 N
---------------------------------------	------

Material specifications

Color	violet
Flammability rating according to UL 94	V0
Ferrule material	Zirconia ceramics
Housing material	Plastic
Outer sheath, material	FRNC

Dimensions

External dimensions

External diameter min.	2 mm
External diameter max.	4.2 mm

Mechanical characteristics

Ferrule diameter	2.50 mm
------------------	---------

Connection data

Connection technology

Connection method	SC duplex
-------------------	-----------

Conductor connection

Connection method	SC duplex
-------------------	-----------

Connector

Connection 1

Type	Plug straight SC duplex
Degree of protection	IP20

Connection 2

FOC-SC:A-SC:A-GZ03/... - FO patch cable



1405699

<https://www.phoenixcontact.com/us/products/1405699>

Type	Plug straight SC duplex
Degree of protection	IP20

Cable/line

Cable weight	8.30 kg/km
Cable type	Fiberglass
Cable type	Zip cord
External cable diameter	2.00 mm (Zip cord)
Outer sheath, material	LSZH
External sheath, color	violet
Wire diameter incl. insulation	900 µm
Individual wire diameter	900 µm (low-bend)
Single wire, color	-
Tensile strength short-term/long-term	600 N
Smallest bending radius, fixed installation	15 mm
Smallest bending radius, movable installation	30 mm
Cable, attenuation	2.5 dB/km (at 850 nm), 0.7 dB/km (at 1300 nm)
Halogen-free	complying with IEC 60754-1/2
Flame resistance	yes

FO cable

Number of fibers	2
Fiber type	Multimode

Standards and regulations

Flame resistance	yes
Resistance to oil	no

1405699

<https://www.phoenixcontact.com/us/products/1405699>

Classifications

ECLASS

ECLASS-13.0	27061003
ECLASS-15.0	27061003

ETIM

ETIM 10.0	EC002700
-----------	----------

UNSPSC

UNSPSC 21.0	26121600
-------------	----------

FOC-SC:A-SC:A-GZ03/... - FO patch cable



1405699

<https://www.phoenixcontact.com/us/products/1405699>

Environmental product compliance

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com