

FOC-ST:A-LC:A-GZ01/... - FO patch cable




1405706

<https://www.phoenixcontact.com/us/products/1405706>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Assembled FO cable, zip cord cable, multi-mode fiberglass 50/125 μm , OM2, plug: B-FOC (ST)/LC, degree of protection: IP20, for installation in cable ducts or control cabinets



Your advantages

- Multimode patch cable with outstanding optical and mechanical properties for indoor installation
- Ideal for use in distributor systems and for connecting termination devices
- Fire protection with LSZH sheath and UL 94 V0 components
- Interferometer tests at every stage of the certification process
- Satisfies optical and mechanical industry standards
- Connector with UPC polishing for optimum attenuation values

Commercial data

Item number	1405706
Packing unit	1 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Sales key	AB50
Product key	ABNIBC
Customs tariff number	85447000
Country of origin	DE

1405706

<https://www.phoenixcontact.com/us/products/1405706>

Technical data

Product properties

Product type	Data cable preassembled
Application	Standard
Number of positions	2
No. of conductors	2
Number of slots	2

Electrical properties

Transmission medium	Multi-mode fiberglass
Transmission speed	1 Gbps
Transmission speed	1 Gbps

Mechanical properties

Tensile strength short-term/long-term	50 N
---------------------------------------	------

Material specifications

Color	orange
Flammability rating according to UL 94	V0
Ferrule material	Zirconia ceramics
Housing material	Plastic
Outer sheath, material	FRNC

Dimensions

External dimensions

External diameter min.	2 mm
External diameter max.	4.2 mm

Mechanical characteristics

Ferrule diameter	2.50 mm
------------------	---------

Connector

Connection 1

Type	Plug straight 2x ST
Degree of protection	IP20

Connection 2

Type	Plug straight LC
Degree of protection	IP20

Cable/line

Cable weight	8.30 kg/km
Cable type	Fiberglass

FOC-ST:A-LC:A-GZ01/... - FO patch cable



1405706

<https://www.phoenixcontact.com/us/products/1405706>

Cable type	Zip cord
External cable diameter	2.00 mm (Zip cord)
Outer sheath, material	LSZH
External sheath, color	orange
Wire diameter incl. insulation	900 µm
Individual wire diameter	900 µm
Single wire, color	-
Tensile strength short-term/long-term	600 N
Smallest bending radius, fixed installation	30 mm
Smallest bending radius, movable installation	60 mm
Cable, attenuation	2.7 dB/km (at 850 nm); 0.8 dB/km (at 1300 nm)
Halogen-free	complying with IEC 60754-1/2
Flame resistance	yes

FO cable

Number of fibers	2
Fiber type	Multimode

Standards and regulations

Flame resistance	yes
Resistance to oil	no

FOC-ST:A-LC:A-GZ01/... - FO patch cable



1405706

<https://www.phoenixcontact.com/us/products/1405706>

Classifications

ECLASS

ECLASS-13.0	27061003
ECLASS-15.0	27061003

ETIM

ETIM 10.0	EC002700
-----------	----------

UNSPSC

UNSPSC 21.0	26121600
-------------	----------

1405706

<https://www.phoenixcontact.com/us/products/1405706>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com