

NBC-M12MS/ 2,2-94C/M12FR NHF - Network cable



1407866

<https://www.phoenixcontact.com/us/products/1407866>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Network cable, Ethernet, 8-position, shielded, Plug straight M12, on Socket angled M12, cable length: 2.2 m

Commercial data

Item number	1407866
Packing unit	1 pc
Minimum order quantity	25 pc
Product key	AF1CMI
GTIN	4046356779623
Weight per piece (including packing)	185.6 g
Weight per piece (excluding packing)	182 g
Country of origin	PL

1407866

<https://www.phoenixcontact.com/us/products/1407866>

Technical data

Product properties

Product type	Data cable preassembled
Number of positions	8

Interfaces

Bus system	Ethernet
Signal type/category	Ethernet

Electrical properties

Nominal voltage U_N	30 V AC
	30 V DC

Material specifications

Outer sheath, material	PUR
------------------------	-----

Connector

Connection 1

Type	Plug straight M12
------	-------------------

Connection 2

Type	Socket angled M12
------	-------------------

Cable/line

Cable length	2.2 m
Signal type/category	Ethernet
Outer sheath, material	PUR
External sheath, color	water blue RAL 5021

NBC-M12MS/ 2,2-94C/M12FR NHF - Network cable



1407866

<https://www.phoenixcontact.com/us/products/1407866>

Classifications

ECLASS

ECLASS-13.0	27060307
ECLASS-15.0	27060307

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com