

CUC-PP-PATCHBAY - Marshalling panel



1407994

<https://www.phoenixcontact.com/us/products/1407994>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Marshalling panel, design: 19" rack/fixe housing, degree of protection: IP20, material: Steel, powder-coated, connection method: Screw connection, color: light gray RAL 7035



Jumpering panel, 19" (gray, with 5 plastic brackets)

Product description

Marshalling distributor panel, 19", 1 RU, with 5 plastic brackets

Your advantages

- For easy cable management

Commercial data

Item number	1407994
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	AB18
Product key	ABNLBZ
GTIN	4046356788076
Weight per piece (including packing)	387 g
Weight per piece (excluding packing)	387 g
Customs tariff number	39269097
Country of origin	DE

CUC-PP-PATCHBAY - Marshalling panel



1407994

<https://www.phoenixcontact.com/us/products/1407994>

Technical data

Product properties

Product type	Data plug
Type	1RU

Connection data

Connection method	Screw connection
-------------------	------------------

Dimensions

Width	482.6 mm
Height	44.45 mm
Drill hole distance, horizontal	31.6 mm

Material specifications

Color	light gray RAL 7035
Material	Steel, galvanized
Flammability rating according to UL 94	V0
Housing material	Steel, powder-coated
Housing surface material	Powder-coated, gray

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP20
	IP20
Ambient temperature (operation)	-20 °C ... 60 °C
Ambient temperature (storage/transport)	-40 °C ... 70 °C
Ambient temperature (assembly)	-10 °C ... 60 °C

CUC-PP-PATCHBAY - Marshalling panel



1407994

<https://www.phoenixcontact.com/us/products/1407994>

Classifications

ECLASS

ECLASS-13.0	19170192
ECLASS-15.0	19170192

ETIM

ETIM 10.0	EC003626
-----------	----------

UNSPSC

UNSPSC 21.0	26121600
-------------	----------

CUC-PP-PATCHBAY - Marshalling panel



1407994

<https://www.phoenixcontact.com/us/products/1407994>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com