

CUC-PP-FRAME-19 BK - 19" mounting frame



1409140

<https://www.phoenixcontact.com/us/products/1409140>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

19" frame, empty modular distribution panel, for using 8 modules (6 x RJ45 each) with 48 connections in total, 1 HE, color similar to RAL 9005



19" mounting frame (black)

Product description

19" frame, empty, for using 8 modules (6x RJ45 each) with 48 connections in total, 1 RU, color similar to RAL 9005

Commercial data

| | |
|--------------------------------------|--------------------------------|
| Item number | 1409140 |
| Packing unit | 1 pc |
| Note | Made to order (non-returnable) |
| Sales key | NULL |
| Product key | ABNMAY |
| GTIN | 4046356862462 |
| Weight per piece (including packing) | 1,532 g |
| Weight per piece (excluding packing) | 1,532 g |
| Customs tariff number | 85389099 |
| Country of origin | DE |

CUC-PP-FRAME-19 BK - 19" mounting frame



1409140

<https://www.phoenixcontact.com/us/products/1409140>

Technical data

Product properties

| | |
|-----------------|---|
| Number of slots | 8 |
|-----------------|---|

Connection data

| | |
|-------------------|--|
| Connection method | Screw connection (in connection with the base element) |
|-------------------|--|

Dimensions

| | |
|---------------------------------|----------|
| Width | 482.6 mm |
| Height | 44.45 mm |
| Depth | 184 mm |
| Drill hole distance, horizontal | 31.6 mm |

Material specifications

| | |
|--|----------------------|
| Material | Steel, galvanized |
| Flammability rating according to UL 94 | V0 |
| Housing material | Steel, powder-coated |
| Housing surface material | Powder-coated, black |

Environmental and real-life conditions

Ambient conditions

| | |
|---|------------------|
| Degree of protection | IP20 |
| | IP20 |
| Ambient temperature (operation) | -20 °C ... 60 °C |
| Ambient temperature (storage/transport) | -40 °C ... 70 °C |
| Ambient temperature (assembly) | -10 °C ... 60 °C |

CUC-PP-FRAME-19 BK - 19" mounting frame



1409140

<https://www.phoenixcontact.com/us/products/1409140>

Environmental product compliance

EU RoHS

| | |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

China RoHS

| | |
|--|--|
| Environment friendly use period (EFUP) | EFUP-E |
| | No hazardous substances above the limits |

EU REACH SVHC

| | |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com