

# SACC-CI-M12FS-2CON-L180 THR - Contact carrier



1413874

<https://www.phoenixcontact.com/us/products/1413874>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Contact carrier, 2-position, Socket, M12, A-coding, THR solder connection, this item is expected to be lead-free from Q1 2026 in accordance with RoHS II without exception 6c (Pb < 0.1%), a lead-free alternative is possible on request in advance

## Commercial data

Item number	1413874
Packing unit	60 pc
Minimum order quantity	60 pc
Product key	ABQAGS
GTIN	4055626074412
Weight per piece (including packing)	4.336 g
Weight per piece (excluding packing)	1.812 g
Country of origin	DE

1413874

<https://www.phoenixcontact.com/us/products/1413874>

## Technical data

### Product properties

Product type	Contact insert
Number of positions	2
Coding	A
Thread type	M12

### Connection data

Connection method	THR solder connection
-------------------	-----------------------

### Connector

#### Connection 1

Head design	Socket
Head thread type	M12
Coding	A

### Environmental and real-life conditions

#### Ambient conditions

UL Type Rating	Type 4 (indoor use only)
----------------	--------------------------

# SACC-CI-M12FS-2CON-L180 THR - Contact carrier





1413874

<https://www.phoenixcontact.com/us/products/1413874>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1413874>

 <b>UL Recognized</b> Approval ID: E118976-20100522				
	Nominal voltage $U_N$	Nominal current $I_N$	Cross section AWG	Cross section $\text{mm}^2$
keine				
	250 V	4 A	22	-

 <b>cULus Recognized</b> Approval ID: E221474-20140616				
	Nominal voltage $U_N$	Nominal current $I_N$	Cross section AWG	Cross section $\text{mm}^2$
keine				
	250 V	4 A	-	-

# SACC-CI-M12FS-2CON-L180 THR - Contact carrier



1413874

<https://www.phoenixcontact.com/us/products/1413874>

## Classifications

### ECLASS

ECLASS-13.0	27440223
ECLASS-15.0	27440223

### ETIM

ETIM 10.0	EC003557
-----------	----------

### UNSPSC

UNSPSC 21.0	39121400
-------------	----------

1413874

<https://www.phoenixcontact.com/us/products/1413874>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c)

### China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

### EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	078588bf-d3d4-499e-9b5c-2f66b56a06e6

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)