

# CUC-PP-MODUL-RJ45:N01 - RJ45 connector



1414040

<https://www.phoenixcontact.com/us/products/1414040>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Module, RJ45 each with 6 x RJ45 10 Gbps (Class E<sub>A</sub>)

## Commercial data

Item number	1414040
Packing unit	1 pc
Note	Made to order (non-returnable)
Sales key	NULL
Product key	ABNMAY
GTIN	4055626014623
Weight per piece (including packing)	247 g
Weight per piece (excluding packing)	22.22 g
Customs tariff number	85366990
Country of origin	DE

# CUC-PP-MODUL-RJ45:N01 - RJ45 connector



1414040

<https://www.phoenixcontact.com/us/products/1414040>

## Technical data

### Product properties

Type	19" rack patch module
Number of positions	48
Number of slots	6

### Electrical properties

Rated voltage (III/3)	72 V (DC)
Transmission speed	10 Gbps

### Material specifications

Color	Bare metallic
Flammability rating according to UL 94	V0
Housing material	Stainless steel

### Cable/line

External cable diameter	18 mm ... 18 mm (AWG 23)
-------------------------	--------------------------

### Mechanical properties

#### Mechanical data

Insertion/withdrawal cycles	≥ 750
-----------------------------	-------

### Environmental and real-life conditions

#### Ambient conditions

Degree of protection	IP20
	IP20
Ambient temperature (operation)	-20 °C ... 60 °C
Ambient temperature (storage/transport)	-40 °C ... 70 °C
Ambient temperature (assembly)	-10 °C ... 60 °C

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)