

HC-D25-BCSFS-PRBK - Protective cover



1414642

<https://www.phoenixcontact.com/us/products/1414642>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Protective cover D25, for single locking latch, protective cover material: PA, height: 20.5 mm, seal: yes

Commercial data

Item number	1414642
Packing unit	1 pc
Note	Made to order (non-returnable)
Sales key	BF66
Product key	AF7AZC
GTIN	4055626030944
Weight per piece (including packing)	20.3 g
Weight per piece (excluding packing)	20.3 g
Customs tariff number	85389099
Country of origin	DE

HC-D25-BCSFS-PRBK - Protective cover



1414642


<https://www.phoenixcontact.com/us/products/1414642>

Technical data

Product properties

Product type	Protective cover
Housing type	Protective cover
Type	D25
Seal present	yes

Dimensions

Dimensional drawing	
Width	32.5 mm
Height	20.5 mm
Length	79.5 mm

Material specifications

Material Protective cover	PA
Flammability rating according to UL 94	V2
Seal material	NBR
Material, protective cover	PA

Mechanical properties

Mechanical data

Locking type	Pin
--------------	-----

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP66
Ambient temperature (operation)	-20 °C ... 100 °C

Mounting

Assembly note	Double eyelet for mounting on a cable / below screw head
	Plastic protective cover for short-term protection

HC-D25-BCSFS-PRBK - Protective cover




1414642

<https://www.phoenixcontact.com/us/products/1414642>

Drawings

Dimensional drawing



Dimensional drawing

HC-D25-BCSFS-PRBK - Protective cover



1414642

<https://www.phoenixcontact.com/us/products/1414642>

Classifications

ECLASS

ECLASS-13.0	27440208
ECLASS-15.0	27440208

HC-D25-BCSFS-PRBK - Protective cover



1414642

<https://www.phoenixcontact.com/us/products/1414642>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com