# MD-INB24-3-SZP-S - Module plate

1415242

https://www.phoenixcontact.com/us/products/1415242

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Module plate, with seal, for CES B24 sealing frames, with 3 openings, including mounting screws



## Product description

Module plate
8 mounting screws (M5x12) /
and
Washers are supplied as standard

## Commercial data

| | |
|---|---|
| Item number | 1415242 |
| Packing unit | 1 pc |
| Minimum order quantity | 1 pc |
| Sales key | BF67 |
| Product key | AF7CZX |
| GTIN | 4055626039473 |
| Weight per piece (including packing) | 776 g |
| Weight per piece (excluding packing) | 776 g |
| Customs tariff number | 73269098 |
| Country of origin | DE |

## Technical data

### Notes

| | |
|---|---|
| General | incl. mounting screws |


### Product properties

| | |
|---|---|
| Product type | Adapter plate |
| Seal present | yes |

### Connection data

| | |
|---|---|
| Tightening torque | 1 ... 1.2 Nm |

### Dimensions

| | |
|---|---|
| Dimensional drawing |  |
| Width | 168 mm |
| Height | 2 mm |
| Length | 338 mm |

### Material specifications

| | |
|---|---|
| Material | Stainless steel 1.4301/AISI 304 |
| Material grommet GRP | NBR |

### Environmental and real-life conditions

#### Ambient conditions


| | |
|---|---|
| Degree of protection | IP54 |
| Ambient temperature (operation) | -40 °C ... 100 °C |

### Mounting


| | |
|---|---|
| Assembly note | Diameter of fixing hole for self-tapping screw: 4.5 mm ... 4.7 mm, mounting screws (M5x12): 1.0 Nm ... 1.2 Nm tightening torque, SW4 Allen key |
| | Make sure the seal is fitted correctly (must not be be squeezed out at the sides) |

## Drawings

Dimensional drawing



Dimensional drawing




Wall cutout drawing

## Classifications

### ECLASS

| | |
|---|---|
| ECLASS-13.0 | 27440201 |
| ECLASS-15.0 | 27440201 |

### ETIM

| | |
|---|---|
| ETIM 10.0 | EC002309 |

### UNSPSC

| | |
|---|---|
| UNSPSC 21.0 | 31261500 |

## Environmental product compliance

China RoHS

| | |
|---|---|
| Environment friendly use period (EFUP) | EFUP-E |
| | No hazardous substances above the limits |

EU REACH SVHC

| | |
|---|---|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |

Phoenix Contact 2026 © - all rights reserved
https://www.phoenixcontact.com

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com