

HC-STA-D07-HCLWS-PLR-BK - Protective cover



1419274

<https://www.phoenixcontact.com/us/products/1419274>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Protective cover D7, with single locking latch, material: PA, protective cover material: PA, height: 30 mm, seal: yes, Standard, with lanyard, for socket inserts



Commercial data

| | |
|--------------------------------------|---------------|
| Item number | 1419274 |
| Packing unit | 1 pc |
| Minimum order quantity | 1 pc |
| Sales key | BF66 |
| Product key | AF7AZC |
| GTIN | 4055626160252 |
| Weight per piece (including packing) | 14 g |
| Weight per piece (excluding packing) | 13.6 g |
| Customs tariff number | 85389099 |
| Country of origin | CN |

1419274


<https://www.phoenixcontact.com/us/products/1419274>

Technical data

Product properties

| | |
|------------------------|------------------|
| Product type | Protective cover |
| Housing type | Protective cover |
| Application | Standard |
| Type | D7 |
| Retaining cord present | yes |
| Seal present | yes |

Dimensions

| | |
|---------------------|--|
| Dimensional drawing |  |
| Width | 24.2 mm |
| Height | 30 mm |
| Length | 24.2 mm |
| Diameter | 25 mm |

Material specifications

| | |
|--|--|
| Color | black (RAL 9005) |
| Material Protective cover | PA |
| Flammability rating according to UL 94 | V0 (Polyamide housing) V0 (Locking latch) |
| Seal material | NBR |
| Housing material | PA |
| Material, protective cover | PA |
| Locking latch material | PA |

Mechanical properties

Mechanical data

| | |
|--------------|-------|
| Locking type | Latch |
|--------------|-------|

Environmental and real-life conditions

Ambient conditions

| | |
|---------------------------------|-------------------|
| Degree of protection | IP66 |
| Ambient temperature (operation) | -20 °C ... 100 °C |

Mounting


| | |
|---------------|--|
| Assembly note | Plastic protective cover for short-term protection |
|---------------|--|

1419274

<https://www.phoenixcontact.com/us/products/1419274>

Drawings

Dimensional drawing



Dimensional drawing

HC-STA-D07-HCLWS-PLR-BK - Protective cover



1419274

<https://www.phoenixcontact.com/us/products/1419274>

Approvals

🔗 To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1419274>

DNV

Approval ID: TAE000037S

1419274

<https://www.phoenixcontact.com/us/products/1419274>

Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-13.0 | 27440208 |
| ECLASS-15.0 | 27440208 |

ETIM

| | |
|-----------|----------|
| ETIM 10.0 | EC002314 |
|-----------|----------|

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 39121400 |
|-------------|----------|

1419274

<https://www.phoenixcontact.com/us/products/1419274>

Environmental product compliance

EU RoHS

| | |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

China RoHS

| | |
|--|--|
| Environment friendly use period (EFUP) | EFUP-E |
| | No hazardous substances above the limits |

EU REACH SVHC

| | |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com