

# CUC-DST-GZNI-A/DSSC15 - D-SUB sleeve housings



1419725

<https://www.phoenixcontact.com/us/products/1419725>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

D-SUB sleeve housings, degree of protection: IP20, material: Die-cast zinc, cable outlet: angled, housing size: 2, color: Bare metallic



## Your advantages

- Easy to mount thanks to preassembled locking screws
- Angled conductor entry
- Antimagnetic plastic housing

## Commercial data

Item number	1419725
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	AB19
Product key	ABNCAE
GTIN	4055626188041
Weight per piece (including packing)	55.3 g
Weight per piece (excluding packing)	55.3 g
Customs tariff number	85389099
Country of origin	DE

1419725

<https://www.phoenixcontact.com/us/products/1419725>

## Technical data

### Product properties

Product type	Sleeve housings
Type	D-SUB
No. of cable outlets	1
Cable outlet	angled

### Connection data

Screw thread	4-40 UNC
--------------	----------

### Dimensions

Width	40 mm
Height	15.2 mm
Depth	57 mm

### Material specifications

Color	Bare metallic
Flammability rating according to UL 94	V0
Housing material	Die-cast zinc
Housing surface material	nickel-plated

### Cable/line

External cable diameter	3 mm ... 8.5 mm (Without bending protection)
-------------------------	--

### Environmental and real-life conditions

#### Ambient conditions


Degree of protection	IP20
Ambient temperature (operation)	-35 °C ... 100 °C

### Mounting

Mounting type	Screw locking mechanism
---------------	-------------------------

Drawings

Schematic diagram



1419725

<https://www.phoenixcontact.com/us/products/1419725>

## Classifications

### ECLASS

ECLASS-13.0	27440202
ECLASS-15.0	27440202

### ETIM

ETIM 10.0	EC000437
-----------	----------

### UNSPSC

UNSPSC 21.0	31261500
-------------	----------

# CUC-DST-GZNI-A/DSSC15 - D-SUB sleeve housings



1419725

<https://www.phoenixcontact.com/us/products/1419725>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)