

FOC-OS4S-LCD2-GF01/0,6 - Distributor cable



1419753

<https://www.phoenixcontact.com/us/products/1419753>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

4-insert LC receptacles, type: circular connector, degree of protection: IP68, number of positions: 4



Product description

Robust 4-position LC receptacle, ODC-4 to ODC-4, threaded locking, degree of protection: IP68

Your advantages

- Compact design with ceramic contact inserts
- Threaded locking latch
- For extreme ambient conditions

Commercial data

Item number	1419753
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	AB15
Product key	ABNHAB
GTIN	4055626187587
Weight per piece (including packing)	68.8 g
Weight per piece (excluding packing)	60.513 g
Customs tariff number	85447000
Country of origin	CN

1419753

<https://www.phoenixcontact.com/us/products/1419753>

Technical data

Product properties

Product type	Data cable preassembled
Number of positions	4
No. of conductors	4

Electrical properties

Attenuation	typ. 0.2 dB
	max. 0.6 dB
Transmission medium	Multi-mode fiberglass

Mechanical properties

Tensile strength short-term/long-term	30 N
---------------------------------------	------

Material specifications

Flammability rating according to UL 94	V0
Ferrule material	Zirconia ceramics
Outer sheath, material	LSFH

Connector

Connection 1

Locking type	Screw locking mechanism
Insertion/withdrawal cycles	1000
Degree of protection	IP68 (IEC 60529)
	IP68
Ambient temperature (operation)	-20 °C ... 70 °C (IEC 60794-1-2 F1)

Connection 2

Locking type	Push Pull
Material	Plastic
Degree of protection	IP20 (IEC 60529)

Cable/line

Cable length	0.6 m
Cable weight	3.00 kg/km
Cable type	Multimode fiberglass
Cable type	Zip cord, fiberglass
Outer sheath, material	LSFH
External sheath, color	orange
Individual wire diameter	250 µm
Tensile strength short-term/long-term	30 N
Halogen-free	complying with IEC 60754-1/2

FOC-OS4S-LCD2-GF01/0,6 - Distributor cable



1419753

<https://www.phoenixcontact.com/us/products/1419753>

FO cable

Number of fibers	4
Fiber	62.5/125 µm OM1
Fiber type	Multimode fiberglass 62.5/125 µm
Transmission medium	Multi-mode fiberglass

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP68
Ambient temperature (operation)	-40 °C ... 85 °C (IEC 61300-2-22)
Shock	100g, according to IEC 61300-2-9

FOC-OS4S-LCD2-GF01/0,6 - Distributor cable



1419753

<https://www.phoenixcontact.com/us/products/1419753>

Classifications

ECLASS

ECLASS-13.0

27061003

ETIM

ETIM 9.0

EC002607

UNSPSC

UNSPSC 21.0

43223300

FOC-OS4S-LCD2-GF01/0,6 - Distributor cable



1419753

<https://www.phoenixcontact.com/us/products/1419753>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
-----------------------------------------	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com