

HC-STA-B10-HLFS-BLANK-EL-AL - Housing



1419902

<https://www.phoenixcontact.com/us/products/1419902>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Sleeve housing B10, for single locking latch, material: Die-cast aluminum, salt water resistant, variable, height: 57 mm, cable gland: none, Standard, Without thread opening for screw connection

Product description

Sleeve housing, without screw thread

Your advantages

- Good shielding in the event of electromagnetic interference

Commercial data

Item number	1419902
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	BF56
Product key	AF7APB
GTIN	4055626201269
Weight per piece (including packing)	156.4 g
Weight per piece (excluding packing)	158.4 g
Customs tariff number	85389099
Country of origin	CN

HC-STA-B10-HLFS-BLANK-EL-AL - Housing



1419902

<https://www.phoenixcontact.com/us/products/1419902>

Technical data


Notes

General	for contact inserts HC-B10, BB18, DD42, M, K8/24, HV03
---------	--

Product properties

Product type	Housing with locking latch
Housing type	Sleeve housing
Application	Standard
Type	B10
Cable outlet	variable
Pg screw connection	none

Dimensions

Dimensional drawing	
Width	44 mm
Height	57 mm
Length	73 mm

Material specifications

Housing material	Die-cast aluminum, salt water resistant
Housing surface material	uncoated

Mechanical properties

Mechanical data

Locking type	Pin
--------------	-----

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP66
	IP67
Enclosure rating (NEMA)	4 (UL 50e)
	4X (UL 50e)
	12 (UL 50e)
Impact strength	IK08
Ambient temperature (operation)	-40 °C ... 125 °C

HC-STA-B10-HLFS-BLANK-EL-AL - Housing


1419902

<https://www.phoenixcontact.com/us/products/1419902>



Drawings

Dimensional drawing



Dimensional drawing

HC-STA-B10-HLFS-BLANK-EL-AL - Housing



1419902

<https://www.phoenixcontact.com/us/products/1419902>

Approvals

💡 To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1419902>

DNV

Approval ID: TAE000037S



EAC

Approval ID: RU C-DE.AI30.B.01102

HC-STA-B10-HLFS-BLANK-EL-AL - Housing



1419902

<https://www.phoenixcontact.com/us/products/1419902>

Classifications

ECLASS

ECLASS-13.0	27440202
ECLASS-15.0	27440202

ETIM

ETIM 10.0	EC000437
-----------	----------

UNSPSC

UNSPSC 21.0	31261500
-------------	----------

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

EF3.1 Climate Change

CO2e kg	3.029 kg CO2e
---------	---------------