

# HC-EVO-D15-SLWS-2SSM20-PLR-BK - Housing



1421463

<https://www.phoenixcontact.com/us/products/1421463>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Surface mounting housing D15, with single locking latch, material: PA 6.6-FR, cable outlets: 2, lateral, 2x M20, height: 52 mm, cable gland: none, Standard, including 2x reducing adapter

## Your advantages

- Flexible cable outlet direction, lateral or straight
- Lower costs than metal version
- Low weight
- Lower risk of condensation

## Commercial data

Item number	1421463
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	BF57
Product key	AF7APN
GTIN	4055626265063
Weight per piece (including packing)	90.4 g
Weight per piece (excluding packing)	90.4 g
Customs tariff number	85389099
Country of origin	PL

1421463


<https://www.phoenixcontact.com/us/products/1421463>

## Technical data

### Product properties

Product type	Housing with locking latch
Housing type	Surface mounting housing
Product family	HC-EVO-D
Application	Standard
Type	D15
No. of cable outlets	2
Type of the screw connection	2x M20
Cable outlet	lateral
Pg screw connection	none

### Dimensions

Dimensional drawing	
Width	51 mm
Height	52 mm
Length	80 mm
Hole diameter	4.5 mm

### Material specifications

Flammability rating according to UL 94	V0 (Housing)
	V0 (Interlock)
Housing material	PA 6.6-FR
Locking latch material	PA

### Mechanical properties

#### Mechanical data

Type of the screw connection	2x M20
Locking type	Latch

### Connection data

Tightening torque	0.8 Nm ... 1.2 Nm (for M4 mounting screws on the surface-mount housing)
-------------------	-------------------------------------------------------------------------

### Mounting

Assembly note	Two M25 to M20 reducing adapters are included
	One of the two openings for the screw connections is sealed but can be broken open using a screwdriver.

1421463

<https://www.phoenixcontact.com/us/products/1421463>

## Environmental and real-life conditions

### Ambient conditions

Degree of protection	IP66
Enclosure rating (NEMA)	12 (UL 50e)
Impact strength	IK08
Ambient temperature (operation)	-40 °C ... 125 °C

# HC-EVO-D15-SLWS-2SSM20-PLR-BK - Housing




1421463

<https://www.phoenixcontact.com/us/products/1421463>

## Drawings

Dimensional drawing



Dimensional drawing

# HC-EVO-D15-SLWS-2SSM20-PLR-BK - Housing



1421463

<https://www.phoenixcontact.com/us/products/1421463>

## Approvals

🔗 To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1421463>

**DNV**

Approval ID: TAE000037S

1421463

<https://www.phoenixcontact.com/us/products/1421463>

## Classifications

### ECLASS

ECLASS-13.0	27440202
ECLASS-15.0	27440202

### ETIM

ETIM 10.0	EC000437
-----------	----------

### UNSPSC

UNSPSC 21.0	31261500
-------------	----------

1421463

<https://www.phoenixcontact.com/us/products/1421463>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
-----------------------------------------	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

### EF3.1 Climate Change

CO2e kg	0.897 kg CO2e
---------	---------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)