

SAC-3P-10,0-PUR/FRS PE PPH DMG - Power cable



1421978

<https://www.phoenixcontact.com/us/products/1421978>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Power cable, 3-position, PUR, black, Plug straight M12, coding: S, on Socket angled M12, coding: S, cable length: 10 m, for AC current up to 16 A/230 V, Customer version, KL DMG PPH MODUL 2854889 KPL. MONTIERT at free cable end

Your advantages

- Easy and safe: 100 % electrically tested plug-in components
- Protection against incorrect connection using special S-coding
- Save time, thanks to installation with SPEEDCON fast locking system

Commercial data

Item number	1421978
Packing unit	1 pc
Minimum order quantity	10 pc
Product key	AF1CBB
GTIN	4055626390345
Weight per piece (including packing)	22.22 g
Weight per piece (excluding packing)	22.22 g
Country of origin	DE

1421978

<https://www.phoenixcontact.com/us/products/1421978>

Technical data

Product properties

Product type	Power cable
Application	Energy supply
Number of positions	3
No. of cable outlets	1
Shielded	no
Coding	S

Insulation characteristics

Overvoltage category	III
Degree of pollution	3

Material specifications

Flammability rating according to UL 94	V0
Material of grip body	PP
Contact material	CuZn
Contact surface material	Au
Contact carrier material	PA
Material for screw connection	Zinc die-cast, nickel-plated

Electrical properties

Insulation resistance	> 100 M Ω
Nominal voltage U_N	230 V AC
	230 V DC
Nominal current I_N	16 A

Mechanical properties

Mechanical data

Insertion/withdrawal cycles	> 100
-----------------------------	-------

Connector

Connection 1

Type	Plug straight M12
Coding type	S (Power)

Connection 2

Type	Socket angled M12
Coding type	S (Power)

Cable/line

Cable length	10 m
Number of positions	3

SAC-3P-10,0-PUR/FRS PE PPH DMG - Power cable



1421978

<https://www.phoenixcontact.com/us/products/1421978>

Shielded	no
Outer sheath, material	PUR
External sheath, color	black


Environmental and real-life conditions

Ambient conditions

Degree of protection	IP65 IP67 (without preloading, as additional test in accordance with IEC 60529)
Ambient temperature (operation) (male connector/female connector)	-25 °C ... 105 °C (Plug / socket)

Drawings

Dimensional drawing




M12 x 1 socket, angled

1421978

<https://www.phoenixcontact.com/us/products/1421978>

Schematic diagram



Pin assignment of M12 socket, 3-pos., S-coded, socket side view

SAC-3P-10,0-PUR/FRS PE PPH DMG - Power cable



1421978

<https://www.phoenixcontact.com/us/products/1421978>

Classifications

ECLASS

ECLASS-13.0	27060327
ECLASS-15.0	27060327

UNSPSC

UNSPSC 21.0	31251501
-------------	----------

1421978

<https://www.phoenixcontact.com/us/products/1421978>

Environmental product compliance

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com