WP-CTA POM 13,0 BK - Protective hose adapter

1422884

https://www.phoenixcontact.com/us/products/1422884

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Protective hose adapter, for corrugated hoses with a nominal size of 13 (10 x 13), corrugated in parallel

Commercial data

Item number	1422884
Packing unit	10 pc
Minimum order quantity	10 pc
Sales key	BF46
Product key	AF1ZVX
GTIN	4055626316567
Weight per piece (including packing)	1.622 g
Weight per piece (excluding packing)	1.69 g
Customs tariff number	39269097
Country of origin	CZ

Technical data

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-25 °C ... 85 °C

Material specifications

Material	POM

Cable/line

External cable diameter	4 mm ... 7 mm

Dimensions

Length	20 mm

Classifications

ECLASS

ECLASS-13.0	27430308
ECLASS-15.0	27430308

ETIM

ETIM 10.0	EC001469

UNSPSC

UNSPSC 21.0	39121300

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%

EF3.1 Climate Change

CO2e kg	0.643 kg CO2e

Phoenix Contact 2026 © - all rights reserved
https://www.phoenixcontact.com

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com