

# CUC-PP-FR19:1U-I-EMPTY:24 - Marshalling panel



1422978

<https://www.phoenixcontact.com/us/products/1422978>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Patch bay, 19" mounting, IP20, with 24 slots selectively for RJ45 cable connection modules, RJ45 coupling modules, LC duplex, SC simplex and MPO, medium gray



19" patch bay, for 24 inserts

## Your advantages

- Assembly without special tools
- Rugged design

## Commercial data

Item number	1422978
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	AB18
Product key	ABNLBA
GTIN	4055626319926
Weight per piece (including packing)	808 g
Weight per piece (excluding packing)	808 g
Customs tariff number	85389099
Country of origin	CN

# CUC-PP-FR19:1U-I-EMPTY:24 - Marshalling panel



1422978

<https://www.phoenixcontact.com/us/products/1422978>

## Technical data

### Product properties

Product type	Patch panel
Application	Installation slots for RJ45 cable connection module, adapter-free, and various FO couplings
Connection profile	RJ45
No. of cable outlets	24
Number of slots	24

### Electrical properties

Insulation resistance	according to IEC 61010-1
Transmission medium	FO

### Connection data

Connection method	Quick connection
-------------------	------------------

### Dimensions

Width	482.6 mm
Height	43.6 mm
Depth	83.4 mm

### Material specifications

Color	gray
Material	Steel, galvanized
Flammability rating according to UL 94	V0
Housing material	PC-GF
Standards/regulations	Steel, galvanized

### Cable/line

Tensile strength short-term/long-term	150N (Modul)
---------------------------------------	--------------

### Mechanical properties

Tensile strength short-term/long-term	150N (Modul)
---------------------------------------	--------------

### Environmental and real-life conditions

#### Ambient conditions

Degree of protection	IP20
	IP20
Ambient temperature (operation)	5 °C ... 55 °C
Ambient temperature (storage/transport)	-5 °C ... 55 °C
Ambient temperature (assembly)	-25 °C ... 55 °C

### Mounting

# CUC-PP-FR19:1U-I-EMPTY:24 - Marshalling panel



1422978

<https://www.phoenixcontact.com/us/products/1422978>

Mounting type	19" rack
Assembly note	Observe the grounding concept

# CUC-PP-FR19:1U-I-EMPTY:24 - Marshalling panel



1422978

<https://www.phoenixcontact.com/us/products/1422978>

## Classifications

### ECLASS

ECLASS-13.0	19170192
ECLASS-15.0	19170192

### ETIM

ETIM 10.0	EC003626
-----------	----------

### UNSPSC

UNSPSC 21.0	39121400
-------------	----------

# CUC-PP-FR19:1U-I-EMPTY:24 - Marshalling panel



1422978

<https://www.phoenixcontact.com/us/products/1422978>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)