

# HC-STA-B48-HHFS-1STP36-EM-AL - Housing



1424858

<https://www.phoenixcontact.com/us/products/1424858>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Sleeve housing B48, for single locking latch, material: Die-cast aluminum, salt water resistant, cable outlets: 1, lateral, 1x Pg36, height: 107.5 mm, cable gland: none, Standard

## Your advantages

- Good shielding in the event of electromagnetic interference

## Commercial data

Item number	1424858
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	BF56
Product key	AF7APB
GTIN	4055626382630
Weight per piece (including packing)	595 g
Weight per piece (excluding packing)	590 g
Customs tariff number	85389099
Country of origin	CN

# HC-STA-B48-HHFS-1STP36-EM-AL - Housing



1424858

<https://www.phoenixcontact.com/us/products/1424858>

## Technical data


### Notes

General	This housing can be combined with cable glands with a maximum wrench size of 58 mm
---------	--

### Product properties

Product type	Housing with locking latch
Housing type	Sleeve housing
Application	Standard
Type	B48
No. of cable outlets	1
Type of the screw connection	1x Pg36
Cable outlet	lateral
Pg screw connection	none

### Dimensions

Dimensional drawing	
Width	90 mm
Height	107.5 mm
Length	132 mm

### Material specifications

Housing material	Die-cast aluminum, salt water resistant
Housing surface material	uncoated

### Mechanical properties

#### Mechanical data

Type of the screw connection	1x Pg36
Locking type	Pin

### Environmental and real-life conditions

#### Ambient conditions

Degree of protection	IP66
	IP67
Enclosure rating (NEMA)	4 (UL 50e)
	4X (UL 50e)
	12 (UL 50e)
Impact strength	IK08

# HC-STA-B48-HHFS-1STP36-EM-AL - Housing



1424858

<https://www.phoenixcontact.com/us/products/1424858>

Ambient temperature (operation)

-40 °C ... 125 °C

# HC-STA-B48-HHFS-1STP36-EM-AL - Housing


1424858

<https://www.phoenixcontact.com/us/products/1424858>



## Drawings

Dimensional drawing



Dimensional drawing

1424858

<https://www.phoenixcontact.com/us/products/1424858>

## Approvals

🔗 To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1424858>

**DNV**

Approval ID: TAE000037S



**cUL Recognized**

Approval ID: E255026



**UL Recognized**

Approval ID: E255026

1424858

<https://www.phoenixcontact.com/us/products/1424858>

## Classifications

### ECLASS

ECLASS-13.0	27440202
ECLASS-15.0	27440202

### ETIM

ETIM 10.0	EC000437
-----------	----------

### UNSPSC

UNSPSC 21.0	31261500
-------------	----------

# HC-STA-B48-HHFS-1STP36-EM-AL - Housing



1424858

<https://www.phoenixcontact.com/us/products/1424858>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)