

SACC-M12FR-6Q SH VARAN - Data connector



1429169

<https://www.phoenixcontact.com/us/products/1429169>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Data connector, VARAN, 6-position, shielded, Socket angled M12, coding: A, Insulation displacement connection, knurl material: Brass, nickel-plated, external cable diameter 4 mm ... 8 mm



Your advantages

- Safe use in the field, thanks to a high degree of protection
- Insulation displacement connection: innovative and time-saving assembly without stripping the single wire
- Reliable signal transmission – 360° shielding in environments with electromagnetic interference

Commercial data

Item number	1429169
Packing unit	1 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Sales key	BF31
Product key	AF2CDM
GTIN	4046356323123
Weight per piece (including packing)	55.1 g
Weight per piece (excluding packing)	55.1 g
Customs tariff number	85366990
Country of origin	DE

SACC-M12FR-6Q SH VARAN - Data connector



1429169

<https://www.phoenixcontact.com/us/products/1429169>

Technical data

Notes

Assembly note	NOTE: Observe the permissible bending radii when routing cables, since the degree of protection may be at risk if the bending forces are too high. Reduce mechanical loads upstream of the connector, e.g., by using cable ties.
---------------	-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------

Mounting

Assembly note	The connector pin assignment can be rotated 45° to the cable outlet
---------------	---------------------------------------------------------------------

Product properties

Product type	Circular connector (cable-side)
Application	Data
Number of positions	6
No. of cable outlets	1
Shielded	yes
Coding	A
Cable outlet	angled

Insulation characteristics

Overvoltage category	II
Degree of pollution	3

Dimensions

External dimensions

Outside diameter	4 mm ... 8 mm
------------------	---------------

Material specifications

Flammability rating according to UL 94	V0
Seal material	Neoprene
Material of grip body	Zinc die-cast, nickel-plated
Contact material	CuSn
Contact surface material	Ni/Au
Contact carrier material	PA 6
Material for screw connection	Brass, nickel-plated

Connection data

Conductor connection

Connection method	Insulation displacement connection
Connection cross section	0.14 mm ² ... 0.34 mm ²
Connection cross section AWG	26 ... 22
	0.4 Nm (M12 knurl)

SACC-M12FR-6Q SH VARAN - Data connector



1429169

<https://www.phoenixcontact.com/us/products/1429169>

Tightening torque	0.8 Nm (Connector with coupling sleeve)
	3 Nm (Pressure nut with coupling sleeve)

Electrical properties

Contact resistance	$\leq 5 \text{ m}\Omega$
Insulation resistance	$\geq 100 \text{ M}\Omega$
Nominal voltage U_N	30 V AC
	30 V DC
Nominal current I_N	2 A

Mechanical properties

Mechanical data

Insertion/withdrawal cycles	≥ 100
-----------------------------	------------

Connector

Connection 1

Head design	Socket
Head cable outlet	angled
Head thread type	M12
Coding	A

Cable/line

Signal type/category	VARAN
----------------------	-------

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP67
Ambient temperature (operation) (male connector/female connector)	-40 °C ... 85 °C

Standards and regulations

M12

Standard designation	M12 connector
Standards/specifications	according to IEC 61076-2-101


SACC-M12FR-6Q SH VARAN - Data connector

1429169

<https://www.phoenixcontact.com/us/products/1429169>

Drawings

Dimensional drawing



M12 x 1 socket, angled, shielded


SACC-M12FR-6Q SH VARAN - Data connector

1429169

<https://www.phoenixcontact.com/us/products/1429169>



Schematic diagram



M12 socket pin assignment, 6-pos., socket side view

SACC-M12FR-6Q SH VARAN - Data connector



1429169

<https://www.phoenixcontact.com/us/products/1429169>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1429169>



EAC

Approval ID: RU C-DE.AI30.B.01102

SACC-M12FR-6Q SH VARAN - Data connector



1429169

<https://www.phoenixcontact.com/us/products/1429169>

Classifications

ECLASS

ECLASS-13.0	27440116
ECLASS-15.0	27440116

ETIM

ETIM 10.0	EC002635
-----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

SACC-M12FR-6Q SH VARAN - Data connector



1429169

<https://www.phoenixcontact.com/us/products/1429169>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
-----------------------------------------	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com