

SAC-4P-M12T/2XM12 FF VA - T distributor



1431416

<https://www.phoenixcontact.com/us/products/1431416>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



T distributor, FOUNDATION Fieldbus, PROFIBUS PA, 4-position, unshielded, Plug straight M12, coding: A, on Socket straight M12, coding: A and Socket straight M12, coding: A, Parallel distributor

Your advantages

- Safe use in the field, thanks to a high degree of protection



Commercial data

Item number	1431416
Packing unit	5 pc
Minimum order quantity	1 pc
Sales key	BF10
Product key	AF1GAA
GTIN	4046356431637
Weight per piece (including packing)	28.5 g
Weight per piece (excluding packing)	27.3 g
Customs tariff number	85366990
Country of origin	DE

SAC-4P-M12T/2XM12 FF VA - T distributor



1431416

<https://www.phoenixcontact.com/us/products/1431416>

Technical data

Notes

Assembly note	NOTE: Observe the permissible bending radii when routing cables, since the degree of protection may be at risk if the bending forces are too high. Reduce mechanical loads upstream of the connector, e.g., by using cable ties.
---------------	---

Product properties

Product type	T-distributor
Sensor type	FOUNDATION Fieldbus
Number of positions	4
No. of cable outlets	2
Shielded	no
Coding	A
Thread type	M12

Insulation characteristics

Overvoltage category	II
Degree of pollution	3

Electrical properties

Insulation resistance	$\geq 100 \text{ M}\Omega$
Nominal voltage U_N	48 V AC
	60 V DC
Nominal current I_N	4 A


Interfaces

Signal type/category	FOUNDATION Fieldbus
	PROFIBUS PA

Signaling

Status display	no
Status display present	no

Dimensions

Dimensional drawing	
Width	33 mm
Height	16 mm
Length	55.8 mm

SAC-4P-M12T/2XM12 FF VA - T distributor



1431416

<https://www.phoenixcontact.com/us/products/1431416>

Material specifications

Flammability rating according to UL 94	HB
Seal material	NBR
Material of grip body	TPU, hardly inflammable, self-extinguishing
Contact material	CuZn
Contact surface material	Ni/Au
Contact carrier material	TPU GF
Material for screw connection	Stainless steel

Connector

Connection 1

Type	Plug straight M12
Coding type	A

Connection 2

Type	Socket straight M12
Coding type	A

Connection 3

Type	Socket straight M12
Coding type	A

Cable/line

Signal type/category	FOUNDATION Fieldbus
	PROFIBUS PA

Mechanical properties

Mechanical data

Insertion/withdrawal cycles	≥ 100
-----------------------------	-------

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP65
	IP67
	IP68
	IP69K
Ambient temperature (operation) (male connector/female connector)	-25 °C ... 90 °C (Plug / socket)

Standards and regulations

Standard designation	M12 connector
Standards/specifications	IEC 61076-2-101


SAC-4P-M12T/2XM12 FF VA - T distributor

1431416

<https://www.phoenixcontact.com/us/products/1431416>

Drawings

Dimensional drawing



M12 T-distributor

SAC-4P-M12T/2XM12 FF VA - T distributor



1431416

<https://www.phoenixcontact.com/us/products/1431416>

Schematic diagram



Pin assignment M12 plug, 4-pos., A-coded, view plug side

SAC-4P-M12T/2XM12 FF VA - T distributor

1431416


<https://www.phoenixcontact.com/us/products/1431416>

Schematic diagram



Pin assignment M12 socket, 4-pos., A-coded, view female side

Circuit diagram



Contact assignment of the M12 T distributor

SAC-4P-M12T/2XM12 FF VA - T distributor



1431416

<https://www.phoenixcontact.com/us/products/1431416>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1431416>



EAC

Approval ID: RU C-DE.AI30.B.01102



UL Listed

Approval ID: FILE E 221474

	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
keine				
	250 V	4 A	-	-



cUL Listed

Approval ID: FILE E 221474

	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
keine				
	250 V	4 A	-	-

SAC-4P-M12T/2XM12 FF VA - T distributor



1431416

<https://www.phoenixcontact.com/us/products/1431416>

Classifications

ECLASS

ECLASS-13.0	27440106
ECLASS-15.0	27440106

ETIM

ETIM 10.0	EC002925
-----------	----------

UNSPSC

UNSPSC 21.0	31251500
-------------	----------

SAC-4P-M12T/2XM12 FF VA - T distributor



1431416

<https://www.phoenixcontact.com/us/products/1431416>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

EF3.1 Climate Change

CO2e kg	1.965 kg CO2e
---------	---------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com