

SACC-M12-SCO PLUG L90 - Housing screw connection

1436709

<https://www.phoenixcontact.com/us/products/1436709>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Housing screw connection, Pin, straight, M12-SPEEDCON, this item is expected to be lead-free from Q2 2026 in accordance with RoHS II without exception 6c (Pb < 0.1%), a lead-free alternative is possible on request in advance

Your advantages

- Easy device integration, thanks to mechanical port screw connections with threaded fastening
- Flexible PCB assembly: two-piece connectors for wave and THR soldering
- SPEEDCON fast locking system reduces cabling times

Commercial data

Item number	1436709
Packing unit	10 pc
Minimum order quantity	10 pc
Sales key	AB23
Product key	ABQAEA
GTIN	4046356438773
Weight per piece (including packing)	6.036 g
Weight per piece (excluding packing)	5.73 g
Customs tariff number	79070000
Country of origin	DE

SACC-M12-SCO PLUG L90 - Housing screw connection



1436709

<https://www.phoenixcontact.com/us/products/1436709>

Technical data

Notes

Order information:	Lock nut is included in the scope of delivery
--------------------	---

Product properties

Product type	Circular connector housing
Thread type	M12

Material specifications

Material Housing	GD-Zn
Material Housing surface	Ni
Material Screw connection	Brass, nickel-plated
Material	HNBR

Connector

Connection 1

Head design	Pin
Head cable outlet	straight
Head thread type	M12
Head locking type	SPEEDCON

Environmental and real-life conditions

Ambient conditions

Degree of protection (when plugged in)	IP67 (correctly plugged in and locked)
Degree of protection	IP67 (correctly plugged in and locked)
Ambient temperature (operation) (male connector/female connector)	-25 °C ... 85 °C -40 °C ... 85 °C (without mechanical actuation)
UL Type Rating	Type 4 (indoor use only)

Standards and regulations

Standard designation	M12 circular connector
Standards/specifications	according to IEC 61076-2-101

Mounting

Mounting type	Front mounting (M12 x 1)
---------------	--------------------------

SACC-M12-SCO PLUG L90 - Housing screw connection



1436709

<https://www.phoenixcontact.com/us/products/1436709>

Classifications

ECLASS

ECLASS-13.0	27440224
ECLASS-15.0	27440224

ETIM

ETIM 10.0	EC003556
-----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

SACC-M12-SCO PLUG L90 - Housing screw connection



1436709

<https://www.phoenixcontact.com/us/products/1436709>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c)

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	73b3b7a9-8986-4f48-a303-ee209a6811b7

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com