

# SAC-3P-MR/10,0-PUR/C-1L-Z SCO - Cable



1439036

<https://www.phoenixcontact.com/us/products/1439036>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Cable, Plug angled M12 SPEEDCON, coding: A, on Valve connector C (8 mm), with 1 LED, Wiring: Z diode, cable length: 10 m

## Commercial data

|                                      |                                |
|--------------------------------------|--------------------------------|
| Item number                          | 1439036                        |
| Packing unit                         | 1 pc                           |
| Minimum order quantity               | 1 pc                           |
| Note                                 | Made to order (non-returnable) |
| Product key                          | AF1DNA                         |
| GTIN                                 | 4046356505185                  |
| Weight per piece (including packing) | 319.6 g                        |
| Weight per piece (excluding packing) | 305.6 g                        |
| Country of origin                    | PL                             |

# SAC-3P-MR/10,0-PUR/C-1L-Z SCO - Cable



1439036

<https://www.phoenixcontact.com/us/products/1439036>

## Technical data

### Product properties

|              |                                            |
|--------------|--------------------------------------------|
| Product type | Sensor/actuator cable with valve connector |
|--------------|--------------------------------------------|

### Electrical properties

|                       |         |
|-----------------------|---------|
| Nominal voltage $U_N$ | 24 V AC |
|                       | 24 V DC |

### Connector

#### Connection 1

|              |                          |
|--------------|--------------------------|
| Type         | Plug angled M12 SPEEDCON |
| Locking type | SPEEDCON                 |
| Coding type  | A                        |

#### Connection 2

|                    |                          |
|--------------------|--------------------------|
| Type               | Valve connector C (8 mm) |
| Protective circuit | Z diode                  |

### Cable/line

|              |      |
|--------------|------|
| Cable length | 10 m |
|--------------|------|

# SAC-3P-MR/10,0-PUR/C-1L-Z SCO - Cable



1439036

<https://www.phoenixcontact.com/us/products/1439036>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1439036>



**EAC-RoHS**

Approval ID: RU D-DE.HB35.B.00387



**CSAus**

Approval ID: 13631

|       | Nominal voltage $U_N$ | Nominal current $I_N$ | Cross section AWG | Cross section $\text{mm}^2$ |
|-------|-----------------------|-----------------------|-------------------|-----------------------------|
| keine |                       |                       |                   |                             |
|       | 24 V                  | 4 A                   | -                 | -                           |

# SAC-3P-MR/10,0-PUR/C-1L-Z SCO - Cable



1439036

<https://www.phoenixcontact.com/us/products/1439036>

## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-13.0 | 27060312 |
| ECLASS-15.0 | 27060312 |

### ETIM

|           |          |
|-----------|----------|
| ETIM 10.0 | EC001855 |
|-----------|----------|

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 31251500 |
|-------------|----------|

1439036

<https://www.phoenixcontact.com/us/products/1439036>

## Environmental product compliance

### EU RoHS

|                                         |        |
|-----------------------------------------|--------|
| Fulfills EU RoHS substance requirements | Yes    |
| Exemption                               | 7(c)-I |

### China RoHS

|                                        |                                                                                                                                                                                                                                   |
|----------------------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Environment friendly use period (EFUP) | EFUP-50                                                                                                                                                                                                                           |
|                                        | An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required. |

### EU REACH SVHC

|                                     |                                            |
|-------------------------------------|--------------------------------------------|
| REACH candidate substance (CAS No.) | Diboron trioxide(CAS: 1303-86-2)           |
|                                     | Lead monoxide (lead oxide)(CAS: 1317-36-8) |

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)