

# PV-1P-100,0/S01-2,5 - Cable reel

1459509

<https://www.phoenixcontact.com/us/products/1459509>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Cable ring, black PE-X, 1-pos., cable length: 100 m



## Commercial data

Item number	1459509
Packing unit	1 pc
Note	Made to order (non-returnable)
Sales key	NULL
Product key	ABLBDX
GTIN	4046356618892
Weight per piece (including packing)	4,411.7 g
Weight per piece (excluding packing)	4,411.7 g
Customs tariff number	85444995
Country of origin	DE

# PV-1P-100,0/S01-2,5 - Cable reel



1459509

<https://www.phoenixcontact.com/us/products/1459509>

## Technical data

### Product properties

Number of positions	1
Shielded	no

### Electrical properties

Nominal current $I_N$	$\leq 41$ A (up to +60 °C)
-----------------------	----------------------------

### Dimensions

Length	100 m
--------	-------

### Material specifications

Outer sheath, material	PE-X
Conductor material	Tin-plated Cu litz wires

### Cable/line

Cable length	2.5 m
--------------	-------

### PV1-F cables [S01]

Shielded	no
Cable weight	45 kg/km
Cable type	PV1-F cables
Cable type (abbreviation)	S01
External cable diameter	5.00 mm $\pm$ 0.2 mm
Outer sheath, material	PE-X
External sheath, color	black-gray RAL 7021
Material, inner sheath	PE-X
Conductor structure, voltage supply	50x 0.25 mm
AWG power supply	14
Thickness, insulation	$\geq 0.50$ mm (Inner sheath)
Cable resistance	8.21 $\Omega$ /m (at 20 °C)
Smallest bending radius, fixed installation	12.5 mm
Smallest bending radius, movable installation	25 mm
Ambient temperature (operation)	-40 °C ... 90 °C

### Environmental and real-life conditions

#### Ambient conditions

Ambient temperature (operation) (Cable, fixed installation)	-40 °C ... 90 °C
---	------------------

### Standards and regulations

Flame resistance	IEC 60332-1-2
Other resistance	Resistance to acids and alkalis
	Resistant to salt water

# PV-1P-100,0/S01-2,5 - Cable reel



1459509

<https://www.phoenixcontact.com/us/products/1459509>

---

Resistant to ozone

# PV-1P-100,0/S01-2,5 - Cable reel



1459509

<https://www.phoenixcontact.com/us/products/1459509>

## Environmental product compliance

### China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)