

HC-B 24-KMQ-H-O1PG21 - Housing

1460329

<https://www.phoenixcontact.com/us/products/1460329>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



HEAVYCON B24 coupling housing, with double locking latch, height: 81.5 mm, with 1 x Pg21 gland, straight cable outlet

Commercial data

| | |
|--------------------------------------|--------------------------------|
| Item number | 1460329 |
| Packing unit | 1 pc |
| Note | Made to order (non-returnable) |
| Sales key | BF55 |
| Product key | AF7AAC |
| GTIN | 4046356696159 |
| Weight per piece (including packing) | 350 g |
| Weight per piece (excluding packing) | 350 g |
| Customs tariff number | 85389099 |
| Country of origin | DE |

HC-B 24-KMQ-H-O1PG21 - Housing

1460329

<https://www.phoenixcontact.com/us/products/1460329>

Technical data


Notes

| | |
|---------|--|
| General | For contact inserts HC-B24, BB46, BBB64, D64, DD108, M |
|---------|--|

Product properties

| | |
|------------------------------|----------------------------|
| Product type | Housing with locking latch |
| Housing type | Coupling housings |
| Application | Standard |
| Type | B24 |
| No. of cable outlets | 1 |
| Type of the screw connection | 1x Pg21 |
| Shielded | no |
| Cable outlet | straight |
| Pg screw connection | none |

Dimensions

| | |
|---------------------|--|
| Dimensional drawing |  |
| Width | 43 mm |
| Height | 82 mm |
| Length | 120 mm |

Material specifications

| | |
|--------------------------|-----------------------------|
| Seal material | NBR |
| Housing material | Die-cast aluminum |
| Housing surface material | Powder-coated, gray |
| Locking latch material | Stainless steel, handle: PA |

Mechanical properties

Mechanical data

| | |
|------------------------------|---------|
| Type of the screw connection | 1x Pg21 |
| Locking type | Latch |

Mounting

| | |
|---------------|-------------------------------------|
| Assembly note | For half and full screw connections |
|---------------|-------------------------------------|

Environmental and real-life conditions

Ambient conditions

| | |
|----------------------|------|
| Degree of protection | IP65 |
|----------------------|------|

HC-B 24-KMQ-H-O1PG21 - Housing

1460329

<https://www.phoenixcontact.com/us/products/1460329>



Ambient temperature (operation)

-40 °C ... 125 °C



HC-B 24-KMQ-H-O1PG21 - Housing

1460329

<https://www.phoenixcontact.com/us/products/1460329>

Drawings

Dimensional drawing



Dimensional drawing

HC-B 24-KMQ-H-O1PG21 - Housing



1460329

<https://www.phoenixcontact.com/us/products/1460329>

Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-13.0 | 27440202 |
| ECLASS-15.0 | 27440202 |

HC-B 24-KMQ-H-O1PG21 - Housing



1460329

<https://www.phoenixcontact.com/us/products/1460329>

Environmental product compliance

EU RoHS

| | |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

China RoHS

| | |
|--|--|
| Environment friendly use period (EFUP) | EFUP-E |
| | No hazardous substances above the limits |

EU REACH SVHC

| | |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com