

HS LC-D5PL-45 - Fiber optic



1474365

<https://www.phoenixcontact.com/us/products/1474365>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Single light guide, passive, rigid, Cylinder head, emission surface: planar, number of displays: 1, (1 row, 1 column), length: 45 mm, ESD protection: <4 kV, can be used for the ME, ME-MAX, ME-IO, ME PLC, and EH housing ranges (housing must be processed)

Your advantages

- Light guides are perfectly matched to electronics housings
- Easy mounting on the PCB using press pins
- Resistance to ESD
- Housing processing available on request
- Enables simple visual status and diagnostic indicators

Commercial data

Item number	1474365
Packing unit	50 pc
Minimum order quantity	1 pc
Sales key	AC05
Product key	ACGABC
GTIN	4063151887933
Weight per piece (including packing)	1.157 g
Weight per piece (excluding packing)	1 g
Customs tariff number	90019000
Country of origin	DE

HS LC-D5PL-45 - Fiber optic



1474365

<https://www.phoenixcontact.com/us/products/1474365>

Technical data

Notes

Assembly note	Please observe the application note in the download area.
General	Distance between LED and light guide of 0.2 mm.

Product properties

Product type	Fiber optic
Number of positions	1
Alignment	Vertical
Conductor type	Single light guide
Head form	Cylinder head
Number of indicators	1 (1 row x 1 column)

Electrical properties

ESD protection	< 4 kV
----------------	--------

Dimensions

Length	45 mm
Diameter	5 mm
Hole diameter	4.2 mm
Dimensions	3 mm (Press-in length)

Material specifications

Color (Light guide)	transparent
Material Light guide	Polycarbonate

Environmental and real-life conditions

Ambient conditions

Max. IP code to attain	IP20
Ambient temperature (operation)	-40 °C ... 85 °C

Mounting

Mounting type	Press-in
---------------	----------

HS LC-D5PL-45 - Fiber optic

1474365

<https://www.phoenixcontact.com/us/products/1474365>



Classifications

ECLASS

ECLASS-15.0	27460404
ECLASS-13.0	27460404

ETIM

ETIM 10.0	EC002943
-----------	----------

HS LC-D5PL-45 - Fiber optic



1474365

<https://www.phoenixcontact.com/us/products/1474365>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com