

# HS LCA-RD 12,5X5-F - Signal light



1474407

<https://www.phoenixcontact.com/us/products/1474407>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Signal light with spade connector, active, rigid, Cylinder head, emission surface: planar, number of displays: 1, (1 row, 1 column), diameter: 12.5 mm

## Commercial data

Item number	1474407
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	AC05
Product key	ACGABC
GTIN	4063151887094
Weight per piece (including packing)	4.04 g
Weight per piece (excluding packing)	3 g
Customs tariff number	90019000
Country of origin	TN

# HS LCA-RD 12,5X5-F - Signal light



1474407

<https://www.phoenixcontact.com/us/products/1474407>

## Technical data

### Notes

Assembly note	Please observe the application note in the download area.
---------------	---

### Product properties

Product type	Light
Number of positions	1
Alignment	Vertical
Conductor type	Signal light with spade connector
Head form	Cylinder head
Number of indicators	1 (1 row x 1 column)

### Dimensions

Diameter	12.5 mm (Aperture diameter)
	5 mm (Lens diameter)
Hole diameter	9.7 mm
Dimensions	34.6 mm

### Material specifications

Color (Lens)	transparent
Color (Housing)	white (RAL 9010)
Material Lens	Polycarbonate
Material Housing	Polycarbonate
Surface characteristics	tin-plated

### Environmental and real-life conditions

#### Ambient conditions

Max. IP code to attain	IP40
Ambient temperature (operation)	-20 °C ... 80 °C

### Mounting

Mounting type	Press-in
---------------	----------

### Packaging specifications

Type of packaging	PE bag
-------------------	--------

# HS LCA-RD 12,5X5-F - Signal light



1474407

<https://www.phoenixcontact.com/us/products/1474407>

## Classifications

### ECLASS

ECLASS-13.0	27110201
ECLASS-15.0	27110201

### ETIM

ETIM 10.0	EC002750
-----------	----------

# HS LCA-RD 12,5X5-F - Signal light



1474407

<https://www.phoenixcontact.com/us/products/1474407>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)