

SAC-4P-100,0-180/0,34 - Cable reel



1501786

<https://www.phoenixcontact.com/us/products/1501786>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

By the meter, Cable reel, PUR halogen-free, orange RAL 2003, 4-wire, color single wire: brown, white, blue, black, cable length: 100 m



Commercial data

Item number	1501786
Packing unit	1 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Sales key	BF11
Product key	AF1LBA
GTIN	4017918813499
Weight per piece (including packing)	2,954 g
Weight per piece (excluding packing)	2,791.6 g
Customs tariff number	85444995
Country of origin	DE

SAC-4P-100,0-180/0,34 - Cable reel



1501786

<https://www.phoenixcontact.com/us/products/1501786>

Technical data

Product properties

Product type	Cable by the meter
Number of positions	4

Cable/line

Cable length	100 m
--------------	-------

PUR halogen-free orange [180]

Cable weight	35 kg/km
Number of positions	4
Shielded	no
Cable type	PUR halogen-free orange [180]
Conductor structure signal line	42x 0.10 mm
AWG signal line	22
Conductor cross-section	0.34 mm ²
Wire diameter incl. insulation	1.55 mm ±0.05 mm
External cable diameter	5.2 mm
Outer sheath, material	PUR
External sheath, color	orange RAL 2003
Conductor material	Bare Cu litz wires
Material wire insulation	TPE
Single wire, color	brown, white, blue, black
Thickness, insulation	0.39 mm (Core insulation) 0.75 mm (Outer cable sheath)
Overall twist	4 wires, twisted
Max. conductor resistance	≤ 57.5 Ω/km
Test voltage	2500 V
Smallest bending radius, fixed installation	52 mm
Smallest bending radius, movable installation	78 mm
Dynamic load capacity (bending)	Max. bending cycles: 4000000, Bending radius: 78 mm, Traversing path: 10 m, Traversing rate: 3 m/s, Acceleration: 10 m/s ²
Ambient temperature (operation)	-25 °C ... 105 °C (cable, fixed installation) -5 °C ... 105 °C (Cable, flexible installation)

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-25 °C ... 105 °C (cable, fixed installation) -5 °C ... 105 °C (Cable, flexible installation)
---------------------------------	--

SAC-4P-100,0-180/0,34 - Cable reel



1501786

<https://www.phoenixcontact.com/us/products/1501786>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1501786>



EAC-RoHS

Approval ID: RU D-DE.HB35.B.00371

SAC-4P-100,0-180/0,34 - Cable reel



1501786

<https://www.phoenixcontact.com/us/products/1501786>

Classifications

ECLASS

ECLASS-13.0	27061801
ECLASS-15.0	27061801

ETIM

ETIM 10.0	EC003249
-----------	----------

UNSPSC

UNSPSC 21.0	26121600
-------------	----------

SAC-4P-100,0-180/0,34 - Cable reel



1501786

<https://www.phoenixcontact.com/us/products/1501786>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com