

SAC-3P- 5,0-PVC/M 8SIFS BK - Sensor/actuator cable



1508433

<https://www.phoenixcontact.com/us/products/1508433>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Sensor/actuator cable, 3-position, PVC, black RAL 9005, free cable end, on Socket straight M8 Snap-in, coding: A, cable length: 5 m

Commercial data

Item number	1508433
Packing unit	5 pc
Minimum order quantity	1 pc
Product key	AF1BBA
GTIN	4017918960001
Weight per piece (including packing)	136.18 g
Weight per piece (excluding packing)	126.702 g
Country of origin	PL

1508433

<https://www.phoenixcontact.com/us/products/1508433>

Technical data

Product properties

Product type	Sensor/actuator cable
Number of positions	3
No. of cable outlets	1
Shielded	no
Coding	A

Insulation characteristics

Overvoltage category	II
Degree of pollution	3

Material specifications

Flammability rating according to UL 94	HB
Seal material	NBR
Material of grip body	TPU, hardly inflammable, self-extinguishing
Contact material	CuSn
Contact surface material	Ni/Au
Contact carrier material	TPU GF

Electrical properties

Insulation resistance	$\geq 100 \text{ M}\Omega$
Nominal voltage U_N	48 V AC
	60 V DC
Nominal current I_N	4 A

Signaling

Status display	no
Status display present	no

Connector

Connection 1

Type	free cable end
------	----------------

Connection 2

Type	Socket straight M8 Snap-in
Number of positions	3
Locking type	Snap-in
Coding type	A

Cable/line

Cable length	5 m
--------------	-----

PVC black [PVC]

SAC-3P- 5,0-PVC/M 8SIFS BK - Sensor/actuator cable



1508433

<https://www.phoenixcontact.com/us/products/1508433>

Dimensional drawing	
Cable weight	29 kg/km
Number of positions	3
Shielded	no
Cable type	PVC black [PVC]
Conductor structure signal line	32x 0.10 mm
AWG signal line	24
Conductor cross-section	3x 0.25 mm ² (Signal line)
Wire diameter incl. insulation	1.25 mm ±0.02 mm
External cable diameter	4.40 mm ±0.15 mm
Outer sheath, material	PVC
External sheath, color	black RAL 9005
Conductor material	Bare Cu litz wires
Material wire insulation	PVC
Single wire, color	brown, blue, black
Thickness, insulation	≥ 0.23 mm (Core insulation)
Thickness, outer sheath	≥ 0.76 mm
Overall twist	3 wires, twisted
Max. conductor resistance	max. 78 Ω/km (at 20 °C)
Insulation resistance	≥ 100 MΩ*km (at 20 °C)
Nominal voltage, cable	≥ 300 V
Test voltage	≤ 3000 V
Flame resistance	As per UL-Style 2464
Ambient temperature (operation)	-25 °C ... 80 °C (cable, fixed installation) -5 °C ... 80 °C (Cable, flexible installation)

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP65 IP67
Ambient temperature (operation)	-25 °C ... 90 °C (Plug / socket) -25 °C ... 80 °C (cable, fixed installation) -5 °C ... 80 °C (Cable, flexible installation)

SAC-3P- 5,0-PVC/M 8SIFS BK - Sensor/actuator cable




1508433

<https://www.phoenixcontact.com/us/products/1508433>

Drawings

Dimensional drawing



M8 snap-in sockets

Schematic diagram




Pin assignment socket M8

1508433

<https://www.phoenixcontact.com/us/products/1508433>

Circuit diagram



Contact assignment of M8 socket

SAC-3P- 5,0-PVC/M 8SIFS BK - Sensor/actuator cable



1508433

<https://www.phoenixcontact.com/us/products/1508433>

Classifications

ECLASS

ECLASS-13.0	27060311
ECLASS-15.0	27060311

UNSPSC

UNSPSC 21.0	31251501
-------------	----------

SAC-3P- 5,0-PVC/M 8SIFS BK - Sensor/actuator cable



1508433

<https://www.phoenixcontact.com/us/products/1508433>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com