

ES-FT-HSC20-S-0.2 AG - Connector



1524936

<https://www.phoenixcontact.com/us/products/1524936>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Connector, Range of articles: HSC, color: silver, number of positions: 14, min. conductor cross-section: 0.14 mm², max. conductor cross-section: 1.5 mm², rated current: 4 A, Connection method: Crimp

Commercial data

Item number	1524936
Packing unit	200 pc
Minimum order quantity	200 pc
Sales key	AB04
Product key	ABLDBA
GTIN	4063151992446
Weight per piece (including packing)	0.845 g
Weight per piece (excluding packing)	0.845 g
Customs tariff number	85366990
Country of origin	CN

Technical data

Product properties

Product type	Connectors for energy storage
Product family	HSC
Number of positions	14

Insulation characteristics

Degree of pollution	2
---------------------	---

Electrical properties

Rated surge voltage	8 kV
Rated surge voltage (II/2)	150 V
Rated current	4 A
Contact resistance	≤ 15 mΩ
Insulation resistance	1000 MΩ

Connection data

Connection method	Crimp
-------------------	-------

Material specifications

Color	silver
Contact surface material	Ag/Sn (tarnish protection)

Cable/line

Single wire, cross section	0.14 mm ² 1.5 mm ²
----------------------------	--

Mechanical properties

Mechanical data

Insertion/withdrawal cycles	100
-----------------------------	-----

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-40 °C ... 125 °C
Ambient temperature (storage/transport)	-40 °C ... 80 °C
Altitude	≤ 4000 m

Standards and regulations

Standards/specifications	TÜV (PPP 51090B)
--------------------------	------------------

ES-FT-HSC20-S-0.2 AG - Connector



1524936

<https://www.phoenixcontact.com/us/products/1524936>

Classifications

ECLASS

ECLASS-13.0	27440204
ECLASS-15.0	27440204

ETIM

ETIM 10.0	EC000796
-----------	----------

ES-FT-HSC20-S-0.2 AG - Connector



1524936

<https://www.phoenixcontact.com/us/products/1524936>

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
China RoHS	
Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com