

ES-HSC20-S-0.2 AG - Connector



1524948

<https://www.phoenixcontact.com/us/products/1524948>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Connector, Range of articles: HSC, color: silver, number of positions: 14, min. conductor cross-section: 0.14 mm², max. conductor cross-section: 1.5 mm², rated current: 4 A, Connection method: Crimp

Commercial data

Item number	1524948
Packing unit	200 pc
Minimum order quantity	200 pc
Sales key	AB04
Product key	ABLDBA
GTIN	4063151992330
Weight per piece (including packing)	0.84 g
Weight per piece (excluding packing)	0.68 g
Customs tariff number	85366990
Country of origin	CN

ES-HSC20-S-0.2 AG - Connector

1524948

<https://www.phoenixcontact.com/us/products/1524948>



Technical data

Product properties

Product type	Connectors for energy storage
Product family	HSC
Number of positions	14

Insulation characteristics

Degree of pollution	2
---------------------	---

Electrical properties

Rated surge voltage	8 kV
Rated surge voltage (II/2)	150 V
Rated current	4 A
Contact resistance	$\leq 15 \text{ m}\Omega$
Insulation resistance	1000 M Ω

Connection data

Connection method	Crimp
-------------------	-------

Material specifications

Color	silver
Contact surface material	Ag/Sn (tarnish protection)

Cable/line

Single wire, cross section	0.14 mm ² 1.5 mm ²
----------------------------	--

Mechanical properties

Mechanical data

Insertion/withdrawal cycles	100
-----------------------------	-----

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-40 °C ... 125 °C
Ambient temperature (storage/transport)	-40 °C ... 80 °C
Altitude	$\leq 4000 \text{ m}$

Standards and regulations

Standards/specifications	TÜV (PPP 51090B)
--------------------------	------------------

ES-HSC20-S-0.2 AG - Connector



1524948

<https://www.phoenixcontact.com/us/products/1524948>

Classifications

ECLASS

ECLASS-13.0	27440204
ECLASS-15.0	27440204

ETIM

ETIM 10.0	EC000796
-----------	----------

ES-HSC20-S-0.2 AG - Connector



1524948

<https://www.phoenixcontact.com/us/products/1524948>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com