

SAC-3P-M12MR/B-1L-S - Valve connector



1534119

<https://www.phoenixcontact.com/us/products/1534119>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Valve connector type B, 11 mm contact spacing, horizontal connector M12



Commercial data

Item number	1534119
Packing unit	1 pc
Note	Made to order (non-returnable)
Sales key	NULL
Product key	AF1GDA
GTIN	4046356026475
Weight per piece (including packing)	35.88 g
Weight per piece (excluding packing)	32.2 g
Customs tariff number	85444290
Country of origin	CZ

SAC-3P-M12MR/B-1L-S - Valve connector



1534119

<https://www.phoenixcontact.com/us/products/1534119>

Technical data

Product properties

Product type	Valve connector adapter
Number of positions	3
No. of cable outlets	1
Coding	A

Insulation characteristics

Overvoltage category	II
Degree of pollution	3

Connection data

Connection method	M12 connector
Tightening torque	0.4 Nm (M12 connector)
	0.6 Nm (Valve connector)

Electrical properties

Insulation resistance	$\geq 100 \text{ M}\Omega$
Nominal voltage U_N	24 V AC
	24 V DC
Nominal current I_N	4 A

Mechanical properties

Mechanical data

Insertion/withdrawal cycles	≥ 100
-----------------------------	------------

Material specifications

Flammability rating according to UL 94	V0
Seal material	TPU
Material housing valve plug	PBT
Contact material	CuSn
Contact surface material	Ni/Au
Contact carrier material	TPU GF
Contact material	CuSn
Valve plug contact insert material	PBT
Contact surface material	Ag
Material for screw connection	Zinc die-cast, nickel-plated

Signaling

Status display	LED (yellow)
Status display present	yes

Connector

SAC-3P-M12MR/B-1L-S - Valve connector



1534119

<https://www.phoenixcontact.com/us/products/1534119>

Connection 1

Type	Plug angled M12
Number of positions	3
Coding type	A

Connection 2

Type	Valve connector B (10 mm)
Number of positions	3
Material	CuSn (Contact)
	Ag (Contact surface)
	PBT (Contact carrier)
	PBT (Housing)
Protective circuit	Z diode

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP65
	IP67
Ambient temperature (operation) (male connector/female connector)	-25 °C ... 85 °C (Valve connector)

Standards and regulations

M12

Standard designation	M12 connector
Standards/specifications	IEC 61076-2-101

Valve connector

Standard designation	Valve connector
Standards/specifications	EN 175301-803


SAC-3P-M12MR/B-1L-S - Valve connector

1534119

<https://www.phoenixcontact.com/us/products/1534119>


Drawings

Dimensional drawing



Valve connector, type B with horizontal M12 plug

Schematic diagram




Pin assignment M12 plug, 3-pos., A-coded, view male side

SAC-3P-M12MR/B-1L-S - Valve connector

1534119


<https://www.phoenixcontact.com/us/products/1534119>

Schematic diagram



Valve connector pin assignment, type B

Circuit diagram



SAC-3P-M12MR/B-1L-S - Valve connector



1534119

<https://www.phoenixcontact.com/us/products/1534119>

Classifications

ECLASS

ECLASS-13.0	27440105
ECLASS-15.0	27440105

SAC-3P-M12MR/B-1L-S - Valve connector



1534119

<https://www.phoenixcontact.com/us/products/1534119>

Environmental product compliance

China RoHS

Environment friendly use period (EFUP)	EFUP-50 An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.
--	--

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com