

SAC-3P- 1,0-PUR/CI-1L-S 110V - Sensor/actuator cable



1535480

<https://www.phoenixcontact.com/us/products/1535480>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Sensor/actuator cable, 3-position, PUR halogen-free, black-gray RAL 7021, Plug straight M12, coding: A, with 1 LED, on Valve connector CI (9.4 mm), with 1 LED, Wiring: Z diode, cable length: 1.5 m

Commercial data

Item number	1535480
Packing unit	1 pc
Note	Made to order (non-returnable)
Sales key	BF07
Product key	AF1DFA
GTIN	4046356027229
Weight per piece (including packing)	82.72 g
Weight per piece (excluding packing)	76.12 g
Customs tariff number	85445190
Country of origin	DE

SAC-3P- 1,0-PUR/CI-1L-S 110V - Sensor/actuator cable



1535480

<https://www.phoenixcontact.com/us/products/1535480>

Technical data

Product properties

Product type	Sensor/actuator cable with valve connector
Number of positions	3
No. of cable outlets	1
Shielded	no
Coding	A

Material specifications

Seal material	TPU
Contact material	CuSn
Valve plug contact insert material	PBT
Contact surface material	Ag

Electrical properties

Rated voltage (III/3)	110 V
-----------------------	-------

Signaling

Status display	1 LED
Status display present	yes

Connector

Connection 1

Type	Plug straight M12
Number of positions	3
Coding type	A

Connection 2

Type	Valve connector CI (9.4 mm)
Number of positions	3
Material	CuSn (Contact)
	Ag (Contact surface)
	PBT (Contact carrier)
	PBT (Housing)
Protective circuit	Z diode

Cable/line


Cable length	1.5 m
--------------	-------

PUR halogen-free black [PUR]

SAC-3P- 1,0-PUR/CI-1L-S 110V - Sensor/actuator cable

1535480

<https://www.phoenixcontact.com/us/products/1535480>

Dimensional drawing	
Cable weight	30 kg/km
UL AWM Style	20549
Number of positions	3
Shielded	no
Cable type	PUR halogen-free black [PUR]
Conductor structure signal line	28x 0.15 mm
AWG signal line	20
Conductor cross-section	3x 0.5 mm ²
Wire diameter incl. insulation	1.5 mm ±0.05 mm (Signal line)
External cable diameter	4.50 mm ±0.2 mm
Outer sheath, material	PUR
External sheath, color	black-gray RAL 7021
Conductor material	Bare Cu litz wires
Material wire insulation	PP
Single wire, color	black 1, black 2, green/yellow
Overall twist	3 wires, twisted
Max. conductor resistance	39 Ω/km (at 20 °C)
Insulation resistance	min. 20 MΩ*km
Nominal voltage, cable	≤ 300 V
Test voltage	≥ 1200 V
Minimum bending radius, fixed installation	5 x D
Minimum bending radius, flexible installation	10 x D
Smallest bending radius, fixed installation	22.5 mm
Smallest bending radius, movable installation	45 mm
Dynamic load capacity (bending)	Max. bending cycles: 15000000, Bending radius: 50 mm, Traversing path: 0.9 m, Traversing rate: 5 m/s, Acceleration: 30 m/s ²
Halogen-free	in accordance with DIN VDE 0472 part 815
Flame resistance	according to DIN VDE 0482 According to DIN EN 50265-2-1
Resistance to oil	in accordance with DIN EN 60811-2-1
Other resistance	largely oil-resistant partly UV-resistant (in accordance with DIN EN ISO 4892-2-A)
Ambient temperature (operation)	-40 °C ... 80 °C (cable, fixed installation) -20 °C ... 80 °C (Cable, flexible installation)

SAC-3P- 1,0-PUR/CI-1L-S 110V - Sensor/actuator cable



1535480

<https://www.phoenixcontact.com/us/products/1535480>

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP67
----------------------	------


SAC-3P- 1,0-PUR/CI-1L-S 110V - Sensor/actuator cable

1535480

<https://www.phoenixcontact.com/us/products/1535480>

Drawings

Dimensional drawing




SAC-3P- 1,0-PUR/CI-1L-S 110V - Sensor/actuator cable

1535480

<https://www.phoenixcontact.com/us/products/1535480>

Schematic diagram



Valve connector connector pin assignment, type CI

Circuit diagram



SAC-3P- 1,0-PUR/CI-1L-S 110V - Sensor/actuator cable



1535480

<https://www.phoenixcontact.com/us/products/1535480>

Classifications

ECLASS

ECLASS-13.0	27060312
ECLASS-15.0	27060312

SAC-3P- 1,0-PUR/CI-1L-S 110V - Sensor/actuator cable



1535480

<https://www.phoenixcontact.com/us/products/1535480>

Environmental product compliance

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com