

# SAC-3P- 3,0-PUR/M 8FS BK SO - Sensor/actuator cable



1539541

<https://www.phoenixcontact.com/us/products/1539541>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Sensor/actuator cable, 3-position, PUR/PVC, black RAL 9005, free cable end, on Socket straight M8, coding: A, cable length: 3 m

## Commercial data

Item number	1539541
Packing unit	1 pc
Note	Made to order (non-returnable)
Sales key	NULL
Product key	AF1BBA
GTIN	4046356080651
Weight per piece (including packing)	83.49 g
Weight per piece (excluding packing)	75.49 g
Customs tariff number	85444290
Country of origin	DE

# SAC-3P- 3,0-PUR/M 8FS BK SO - Sensor/actuator cable



1539541

<https://www.phoenixcontact.com/us/products/1539541>

## Technical data

### Product properties

Product type	Sensor/actuator cable
Number of positions	3
No. of cable outlets	1
Shielded	no
Coding	A

### Insulation characteristics

Overvoltage category	II
Degree of pollution	3

### Material specifications

Flammability rating according to UL 94	HB
Seal material	NBR
Material of grip body	TPU, hardly inflammable, self-extinguishing
Contact material	CuSn
Contact surface material	Ni/Au
Contact carrier material	TPU GF
Material for screw connection	Zinc die-cast, nickel-plated

### Electrical properties

Insulation resistance	$\geq 100 \text{ M}\Omega$
Nominal voltage $U_N$	60 V
Nominal current $I_N$	4 A

### Signaling

Status display	no
Status display present	no

### Connector

#### Connection 1

Type	free cable end
------	----------------

#### Connection 2

Type	Socket straight M8
Number of positions	3
Coding type	A

### Cable/line

Cable length	3 m
--------------	-----

#### PUR/PVC black [350]

Cable weight	27 kg/km
--------------	----------

# SAC-3P- 3,0-PUR/M 8FS BK SO - Sensor/actuator cable



1539541

<https://www.phoenixcontact.com/us/products/1539541>

UL AWM Style	20549
Number of positions	3
Shielded	no
Cable type	PUR/PVC black [350]
Conductor structure signal line	32x 0.10 mm
AWG signal line	24
Conductor cross-section	3x 0.25 mm <sup>2</sup> (Signal line)
Wire diameter incl. insulation	1.32 mm ±0.02 mm
External cable diameter	4.40 mm ±0.15 mm
Outer sheath, material	PUR
External sheath, color	black RAL 9005
Conductor material	Bare Cu litz wires
Material wire insulation	PVC
Single wire, color	brown, blue, black
Thickness, insulation	≥ 0.23 mm (Core insulation)
Inner sheath thickness	approx. 0.35 mm
Thickness, outer sheath	≥ 0.38 mm
Overall twist	3 wires, twisted
Max. conductor resistance	≤ 77.6 Ω/km
Insulation resistance	≥ 100 MΩ*km
Nominal voltage, cable	300 V
Test voltage	2500 V
Smallest bending radius, fixed installation	44 mm
Smallest bending radius, movable installation	44 mm
Dynamic load capacity (bending)	Max. bending cycles: 2000000, Bending radius: 44 mm, Traversing path: 5 m, Traversing rate: 3 m/s
Ambient temperature (operation)	-25 °C ... 80 °C (cable, fixed installation) -5 °C ... 80 °C (Cable, flexible installation)

## Environmental and real-life conditions

### Ambient conditions

Degree of protection	IP65
	IP67
	IP68
Ambient temperature (operation)	-25 °C ... 90 °C (Plug / socket)
	-25 °C ... 80 °C (cable, fixed installation)
	-5 °C ... 80 °C (Cable, flexible installation)


# SAC-3P- 3,0-PUR/M 8FS BK SO - Sensor/actuator cable

1539541

<https://www.phoenixcontact.com/us/products/1539541>

## Drawings

Dimensional drawing



Socket M8 x 1, straight

Schematic diagram



Pin assignment M8 socket, 3-pos., view female side


# SAC-3P- 3,0-PUR/M 8FS BK SO - Sensor/actuator cable



1539541

<https://www.phoenixcontact.com/us/products/1539541>

Circuit diagram



Contact assignment of M8 socket

# SAC-3P- 3,0-PUR/M 8FS BK SO - Sensor/actuator cable



1539541

<https://www.phoenixcontact.com/us/products/1539541>

## Classifications

### ECLASS

ECLASS-13.0	27060311
ECLASS-15.0	27060311

# SAC-3P- 3,0-PUR/M 8FS BK SO - Sensor/actuator cable



1539541

<https://www.phoenixcontact.com/us/products/1539541>

## Environmental product compliance

### China RoHS

Environment friendly use period (EFUP)	EFUP-50 An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.
--	--

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)