

# SAC-6P-MSC/1,0-188/FSC SH SCO - Sensor/actuator cable



1550119

<https://www.phoenixcontact.com/us/products/1550119>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Sensor/actuator cable, 6-position, PUR halogen-free, black-gray RAL 7021, shielded, Plug straight M12 SPEEDCON, coding: C, on Socket straight M12 SPEEDCON, coding: C, cable length: 1 m

## Commercial data

Item number	1550119
Packing unit	50 pc
Minimum order quantity	50 pc
Note	Made to order (non-returnable)
Sales key	BF03
Product key	AF1CNA
GTIN	4046356145992
Weight per piece (including packing)	65 g
Weight per piece (excluding packing)	65 g
Customs tariff number	85444290
Country of origin	CN

# SAC-6P-MSC/1,0-188/FSC SH SCO - Sensor/actuator cable



1550119

<https://www.phoenixcontact.com/us/products/1550119>

## Technical data

### Product properties

Product type	Sensor/actuator cable
Number of positions	6
No. of cable outlets	1
Shielded	yes
Coding	C

### Material specifications

Seal material	NBR
Material of grip body	TPU, hardly inflammable, self-extinguishing
Contact material	CuZn
Contact surface material	Ni/Au
Contact carrier material	TPU GF
Material for screw connection	Brass, nickel-plated

### Electrical properties

Nominal voltage $U_N$	30 V AC
	30 V DC
Nominal current $I_N$	2 A

### Signaling

Status display	no
Status display present	no

### Connector

#### Connection 1

Type	Plug straight M12 SPEEDCON
Number of positions	6
Locking type	SPEEDCON
Coding type	C

#### Connection 2

Type	Socket straight M12 SPEEDCON
Number of positions	6
Locking type	SPEEDCON
Coding type	C

### Cable/line

Cable length	1 m
--------------	-----


PUR halogen-free black [PUR]

# SAC-6P-MS/1,0-188/FSC SH SCO - Sensor/actuator cable



1550119

<https://www.phoenixcontact.com/us/products/1550119>

Dimensional drawing	
Cable weight	34 kg/km
Number of positions	6
Shielded	yes
Cable type	PUR halogen-free black [PUR]
Conductor structure signal line	18x 0.10 mm
AWG signal line	26
Conductor cross-section	6x 0.14 mm <sup>2</sup> (Signal line)
Wire diameter incl. insulation	1 mm ±0.05 mm
External cable diameter	5.2 mm 5.20 mm
Outer sheath, material	PUR
External sheath, color	black-gray RAL 7021
Conductor material	Bare Cu litz wires
Single wire, color	brown, white, black, blue, gray, pink
Smallest bending radius, fixed installation	52 mm
Smallest bending radius, movable installation	52 mm
Dynamic load capacity (bending)	Max. bending cycles: 10000000, Bending radius: 52 mm, Traversing path: 10 m, Traversing rate: 3 m/s, Acceleration: 10 m/s <sup>2</sup>
Dynamic load capacity (torsion)	Torsion: ±180 °/m, Torsion cycles: ≥5000000, Torsional frequency: 35 cycles/min.
Halogen-free	in accordance with DIN VDE 0472 part 815
Flame resistance	in accordance with DIN UL-Style 20549
Resistance to oil	in accordance with DIN EN 60811-2-1
Other resistance	Highly resistant to acids, alkaline solutions and solvents hydrolysis and microbe resistant partly UV-resistant (in accordance with DIN EN ISO 4892-2-A)
Special properties	Flexible cable conduit capable Silicone-free Free of substances which would hinder coating with paint or varnish
Ambient temperature (operation)	-40 °C ... 80 °C (cable, fixed installation) -5 °C ... 80 °C (Cable, flexible installation)

## Environmental and real-life conditions

### Ambient conditions

# SAC-6P-MS/1,0-188/FSC SH SCO - Sensor/actuator cable



1550119

<https://www.phoenixcontact.com/us/products/1550119>

Degree of protection	IP65
	IP67
Ambient temperature (operation) (male connector/female connector)	-25 °C ... 90 °C (Plug / socket)

# SAC-6P-MSC/1,0-188/FSC SH SCO - Sensor/actuator cable



1550119

<https://www.phoenixcontact.com/us/products/1550119>

## Drawings

Dimensional drawing



Plug, M12 x 1, straight, shielded

Dimensional drawing




M12 x 1 socket, straight, shielded

1550119


<https://www.phoenixcontact.com/us/products/1550119>

Schematic diagram



M12 plug pin assignment, 6-pos., pin side view

Schematic diagram



M12 socket pin assignment, 6-pos., socket side view

# SAC-6P-MSC/1,0-188/FSC SH SCO - Sensor/actuator cable



1550119

<https://www.phoenixcontact.com/us/products/1550119>

## Classifications

### ECLASS

ECLASS-13.0	27060311
ECLASS-15.0	27060311

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)