

SAC-5P-MS/ 1,5-100/FS SCO OBS - Sensor/actuator cable



1562136

<https://www.phoenixcontact.com/us/products/1562136>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Sensor/actuator cable, 5-position, Plug straight M12 SPEEDCON, coding: A, on Socket straight M12 SPEEDCON, coding: A, cable length: 1.5 m

as illustration, however, without markers

Commercial data

Item number	1562136
Packing unit	50 pc
Minimum order quantity	50 pc
Note	Made to order (non-returnable)
Product key	AF1CDA
GTIN	4046356291996
Weight per piece (including packing)	106.86 g
Weight per piece (excluding packing)	106.86 g
Country of origin	PL

SAC-5P-MS/ 1,5-100/FS SCO OBS - Sensor/actuator cable



1562136

<https://www.phoenixcontact.com/us/products/1562136>

Technical data

Product properties

Product type	Sensor/actuator cable
Number of positions	5
No. of cable outlets	1
Shielded	no
Coding	A

Insulation characteristics

Overvoltage category	II
Degree of pollution	3

Material specifications

Flammability rating according to UL 94	HB
Seal material	NBR
Material of grip body	TPU, hardly inflammable, self-extinguishing
Contact material	CuSn
Contact surface material	Ni/Au
Contact carrier material	TPU GF
Material for screw connection	Zinc die-cast, nickel-plated

Electrical properties

Insulation resistance	≥ 10 MΩ
Nominal voltage U_N	48 V AC
	60 V DC
Nominal current I_N	4 A

Signaling

Status display	no
Status display present	no

Connector

Connection 1

Type	Plug straight M12 SPEEDCON
Number of positions	5
Locking type	SPEEDCON
Coding type	A

Connection 2

Type	Socket straight M12 SPEEDCON
Number of positions	5
Locking type	SPEEDCON
Coding type	A


SAC-5P-MS/ 1,5-100/FS SCO OBS - Sensor/actuator cable



1562136

<https://www.phoenixcontact.com/us/products/1562136>

Cable/line

Cable length	1.5 m
PUR halogen-free gray [280]	
Dimensional drawing	
Shielded	no
Cable type	PUR halogen-free gray [280]
External cable diameter	4.60 mm

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP65
	IP67
	IP68
Ambient temperature (operation)	-25 °C ... 90 °C (Plug / socket)
	-25 °C ... 80 °C (cable, fixed installation)
	-5 °C ... 80 °C (Cable, flexible installation)

SAC-5P-MS/ 1,5-100/FS SCO OBS - Sensor/actuator cable




1562136

<https://www.phoenixcontact.com/us/products/1562136>


Drawings

Dimensional drawing



Plug, M12 x 1, straight, shielded

Dimensional drawing



M12 x 1 socket, straight

SAC-5P-MS/ 1,5-100/FS SCO OBS - Sensor/actuator cable



1562136


<https://www.phoenixcontact.com/us/products/1562136>

Schematic diagram



Pin assignment M12 male connector, 5-pos., A-coded, male side

Schematic diagram



Pin assignment M12 socket, 5-pos., B-coded, female side

SAC-5P-MS/ 1,5-100/FS SCO OBS - Sensor/actuator cable



1562136

<https://www.phoenixcontact.com/us/products/1562136>

Circuit diagram



Contact assignment of the M12 plug

SAC-5P-MS/ 1,5-100/FS SCO OBS - Sensor/actuator cable




1562136

<https://www.phoenixcontact.com/us/products/1562136>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1562136>

 UL Listed Approval ID: FILE E 221474				
	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
keine				
	125 V	4 A	-	-

 cUL Listed Approval ID: FILE E 221474				
	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
keine				
	125 V	4 A	-	-

SAC-5P-MS/ 1,5-100/FS SCO OBS - Sensor/actuator cable



1562136

<https://www.phoenixcontact.com/us/products/1562136>

Classifications

ECLASS

ECLASS-13.0	27060311
ECLASS-15.0	27060311

ETIM

ETIM 10.0	EC001855
-----------	----------

UNSPSC

UNSPSC 21.0	26121600
-------------	----------

SAC-5P-MS/ 1,5-100/FS SCO OBS - Sensor/actuator cable



1562136

<https://www.phoenixcontact.com/us/products/1562136>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com